

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P755968

Luminaire Tested: LD4D90BD010-EU4DR7070959027-4LBDP1MW

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P755968  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D90BD010-EU4DR7070959027-4LBDP1MW  
Description: 4 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 70° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6577.9 lumens  
Efficiency: N/A  
Efficacy: 66.5 lumens/watt  
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 98.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight

TEST NUMBER: P755968

CATALOG NUMBER: LD4D90BD010-EU4DR7070959027-4LBDP1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P755968  
 CATALOG NUMBER: LD4D90BD010-EU4DR7070959027-4LBDP1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	808038
5°	784023
10°	762168
15°	752170
20°	702370
25°	527661
30°	373015
35°	132129
40°	69475
45°	73999
50°	76627
55°	78063
60°	78558
65°	76888
70°	72581
75°	67206
80°	59649
85°	48390

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 57.5°  
 Luminance: 78575 cd/sqm



TEST NUMBER: P755968

CATALOG NUMBER: LD4D90BD010-EU4DR7070959027-4LBDP1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	674.2	10.3
10°-20°	1849.4	28.1
20°-30°	2036.9	31.0
30°-40°	778.3	11.8
40°-50°	367.5	5.6
50°-60°	365.3	5.6
60°-70°	292.5	4.4
70°-80°	168.1	2.6
80°-90°	45.7	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4560.6	69.3
0°-40°	5338.8	81.2
0°-60°	6071.6	92.3
0°-90°	6577.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6577.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	7396	
5°	7148	674
15°	6650	1849
25°	4377	2037
35°	991	778
45°	479	367
55°	410	365
65°	297	292
75°	159	168
85°	39	46
90°	0	



TEST NUMBER: P755968

CATALOG NUMBER: LD4D90BD010-EU4DR7070959027-4LBDP1MW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	7395.5
2.5°	7318.2
5°	7148.4
7.5°	7006.7
10°	6869.7
12.5°	6753.8
15°	6649.6
17.5°	6397.9
20°	6040.7
22.5°	5270.3
25°	4376.9
27.5°	3810.1
30°	2956.6
32.5°	1909.8
35°	990.6
37.5°	535.1
40°	487.1
42.5°	483.6
45°	478.9
47.5°	468.4
50°	450.8
52.5°	430.9
55°	409.8
57.5°	386.4
60°	359.5
62.5°	329.0
65°	297.4
67.5°	262.3
70°	227.2
72.5°	192.0
75°	159.2
77.5°	125.3
80°	94.8
82.5°	66.7
85°	38.6
87.5°	15.2
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)