

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P755835

Luminaire Tested: LD4D90BD010-EU4DR6070959035-4LBDP1B

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P755835  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D90BD010-EU4DR6070959035-4LBDP1B  
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 60° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6859.1 lumens  
Efficiency: N/A  
Efficacy: 69.4 lumens/watt  
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct


Input Watts (W): 98.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



Downlight

TEST NUMBER: P755835  
CATALOG NUMBER: LD4D90BD010-EU4DR6070959035-4LBDP1B

### Luminous Intensity Polar Plot





TEST NUMBER: P755835

CATALOG NUMBER: LD4D90BD010-EU4DR6070959035-4LBDP1B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93		
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86		
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80		
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75		
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70		
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66		
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62		
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59		
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55		
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53		

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	890038
5°	911930
10°	922940
15°	879221
20°	775203
25°	627011
30°	424124
35°	212532
40°	34474
45°	33747
50°	34421
55°	34936
60°	35903
65°	36738
70°	37600
75°	38036
80°	36683
85°	30588

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 75°  
 Luminance: 38036 cd/sqm



TEST NUMBER: P755835

CATALOG NUMBER: LD4D90BD010-EU4DR6070959035-4LBDP1B

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	794.7	11.6
10°-20°	2150.0	31.3
20°-30°	2313.2	33.7
30°-40°	1005.5	14.7
40°-50°	168.9	2.5
50°-60°	164.2	2.4
60°-70°	140.5	2.0
70°-80°	94.0	1.4
80°-90°	28.1	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5257.9	76.7
0°-40°	6263.4	91.3
0°-60°	6596.5	96.2
0°-90°	6859.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6859.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	8146	
5°	8315	795
15°	7773	2150
25°	5201	2313
35°	1593	1006
45°	218	169
55°	183	164
65°	142	140
75°	90	94
85°	24	28
90°	0	



TEST NUMBER: P755835

CATALOG NUMBER: LD4D90BD010-EU4DR6070959035-4LBDP1B

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	8146.0
2.5°	8375.0
5°	8314.6
7.5°	8333.6
10°	8318.8
12.5°	8147.1
15°	7772.8
17.5°	7270.3
20°	6667.1
22.5°	6021.5
25°	5201.0
27.5°	4159.9
30°	3361.7
32.5°	2590.9
35°	1593.4
37.5°	681.7
40°	241.7
42.5°	222.6
45°	218.4
47.5°	211.0
50°	202.5
52.5°	192.9
55°	183.4
57.5°	173.9
60°	164.3
62.5°	153.7
65°	142.1
67.5°	130.4
70°	117.7
72.5°	103.9
75°	90.1
77.5°	74.2
80°	58.3
82.5°	41.3
85°	24.4
87.5°	8.5
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)