

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P755186

Luminaire Tested: LD4D85BD010-EU4DR7070959027-4LBDP1H

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P755186
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D85BD010-EU4DR7070959027-4LBDP1H
Description: 4 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7938.2 lumens
Efficiency: N/A
Efficacy: 90.5 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 87.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P755186
CATALOG NUMBER: LD4D85BD010-EU4DR7070959027-4LBDP1H

Luminous Intensity Polar Plot





TEST NUMBER: P755186
 CATALOG NUMBER: LD4D85BD010-EU4DR7070959027-4LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	975141
5°	946171
10°	919800
15°	907726
20°	847629
25°	636776
30°	450151
35°	159459
40°	83838
45°	89296
50°	92469
55°	94217
60°	94795
65°	92787
70°	87563
75°	81137
80°	72044
85°	58419

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 94823 cd/sqm



TEST NUMBER: P755186

CATALOG NUMBER: LD4D85BD010-EU4DR7070959027-4LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	813.7	10.3
10°-20°	2231.9	28.1
20°-30°	2458.1	31.0
30°-40°	939.2	11.8
40°-50°	443.4	5.6
50°-60°	440.9	5.6
60°-70°	353.0	4.4
70°-80°	202.9	2.6
80°-90°	55.1	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5503.7	69.3
0°-40°	6442.9	81.2
0°-60°	7327.3	92.3
0°-90°	7938.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7938.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8925	
5°	8627	814
15°	8025	2232
25°	5282	2458
35°	1196	939
45°	578	443
55°	495	441
65°	359	353
75°	192	203
85°	47	55
90°	0	



TEST NUMBER: P755186

CATALOG NUMBER: LD4D85BD010-EU4DR7070959027-4LBDP1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	8924.9
2.5°	8831.7
5°	8626.8
7.5°	8455.8
10°	8290.5
12.5°	8150.6
15°	8024.8
17.5°	7721.0
20°	7290.0
22.5°	6360.2
25°	5282.0
27.5°	4598.1
30°	3568.0
32.5°	2304.7
35°	1195.5
37.5°	645.8
40°	587.8
42.5°	583.6
45°	577.9
47.5°	565.2
50°	544.0
52.5°	520.0
55°	494.6
57.5°	466.3
60°	433.8
62.5°	397.1
65°	358.9
67.5°	316.5
70°	274.1
72.5°	231.7
75°	192.2
77.5°	151.2
80°	114.5
82.5°	80.5
85°	46.6
87.5°	18.4
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)