

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P755121

Luminaire Tested: LD4D85BD010-EU4DR6570959030-4LBDP1H

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P755121
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D85BD010-EU4DR6570959030-4LBDP1H
Description: 4 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7099.3 lumens
Efficiency: N/A
Efficacy: 80.9 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 87.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P755121

CATALOG NUMBER: LD4D85BD010-EU4DR6570959030-4LBDP1H

Luminous Intensity Polar Plot





TEST NUMBER: P755121

CATALOG NUMBER: LD4D85BD010-EU4DR6570959030-4LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93																			
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87																			
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80																			
4	97	89	84	79	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	83	78	73	90	83	77	73	81	76	72	79	75	72	77	74	71	69																			
6	87	78	72	68	86	77	72	68	76	71	67	74	70	67	73	69	66	65																			
7	83	73	67	63	81	73	67	63	71	66	62	70	66	62	69	65	62	60																			
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	57																			
9	75	65	59	55	74	65	59	55	64	58	55	63	58	55	62	58	54	53																			
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	763711
5°	764336
10°	791247
15°	792552
20°	729682
25°	621719
30°	475952
35°	336258
40°	198484
45°	80581
50°	29202
55°	16268
60°	9331
65°	5145
70°	5399
75°	4179
80°	4404
85°	3761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 80581 cd/sqm



TEST NUMBER: P755121

CATALOG NUMBER: LD4D85BD010-EU4DR6570959030-4LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	673.1	9.5
10°-20°	1941.5	27.3
20°-30°	2329.4	32.8
30°-40°	1565.4	22.1
40°-50°	468.6	6.6
50°-60°	82.7	1.2
60°-70°	23.5	0.3
70°-80°	11.5	0.2
80°-90°	3.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4943.9	69.6
0°-40°	6509.3	91.7
0°-60°	7060.6	99.5
0°-90°	7099.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7099.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6990	
5°	6969	673
15°	7007	1941
25°	5157	2329
35°	2521	1565
45°	522	469
55°	85	83
65°	20	24
75°	10	12
85°	3	4
90°	0	



TEST NUMBER: P755121

CATALOG NUMBER: LD4D85BD010-EU4DR6570959030-4LBDP1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	6989.8
2.5°	7019.5
5°	6968.9
7.5°	7074.2
10°	7131.8
12.5°	7117.9
15°	7006.6
17.5°	6734.5
20°	6275.6
22.5°	5735.2
25°	5157.1
27.5°	4504.5
30°	3772.5
32.5°	3109.0
35°	2521.0
37.5°	1939.9
40°	1391.6
42.5°	908.9
45°	521.5
47.5°	276.1
50°	171.8
52.5°	119.2
55°	85.4
57.5°	61.6
60°	42.7
62.5°	27.8
65°	19.9
67.5°	17.9
70°	16.9
72.5°	12.9
75°	9.9
77.5°	8.9
80°	7.0
82.5°	5.0
85°	3.0
87.5°	2.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)