

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P755126

Luminaire Tested: LD4D85BD010-EU4DR6570959030-4LBS1LI

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P755126
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D85BD010-EU4DR6570959030-4LBS1LI
Description: 4 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7846.6 lumens
Efficiency: N/A
Efficacy: 89.5 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct


Input Watts (W): 87.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P755126
CATALOG NUMBER: LD4D85BD010-EU4DR6570959030-4LBS1LI

Luminous Intensity Polar Plot





TEST NUMBER: P755126

CATALOG NUMBER: LD4D85BD010-EU4DR6570959030-4LBS1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100															
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93				93															
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85				85															
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78				78															
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72				72															
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66				66															
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61				61															
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56				56															
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52				52															
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49				49															
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46				46															

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	416098
5°	415050
10°	414695
15°	401911
20°	365889
25°	318850
30°	265190
35°	210129
40°	151658
45°	95811
50°	49937
55°	26546
60°	13947
65°	7670
70°	3210
75°	3543
80°	2455
85°	2077

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 95811 cd/sqm



TEST NUMBER: P755126

CATALOG NUMBER: LD4D85BD010-EU4DR6570959030-4LBS1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	673.8	8.6
10°-20°	1845.0	23.5
20°-30°	2255.2	28.7
30°-40°	1829.8	23.3
40°-50°	911.8	11.6
50°-60°	254.3	3.2
60°-70°	57.8	0.7
70°-80°	15.0	0.2
80°-90°	3.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4773.9	60.8
0°-40°	6603.7	84.2
0°-60°	7769.9	99.0
0°-90°	7846.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7846.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7124	
5°	7080	674
15°	6647	1845
25°	4948	2255
35°	2947	1830
45°	1160	912
55°	261	254
65°	56	58
75°	16	15
85°	3	4
90°	0	



TEST NUMBER: P755126

CATALOG NUMBER: LD4D85BD010-EU4DR6570959030-4LBS1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	7124.5
2.5°	7119.3
5°	7079.5
7.5°	7056.4
10°	6992.6
12.5°	6862.7
15°	6647.1
17.5°	6310.0
20°	5887.0
22.5°	5430.5
25°	4947.9
27.5°	4431.7
30°	3932.3
32.5°	3439.2
35°	2947.2
37.5°	2456.1
40°	1989.2
42.5°	1551.6
45°	1160.0
47.5°	808.2
50°	549.6
52.5°	379.0
55°	260.7
57.5°	175.9
60°	119.4
62.5°	82.7
65°	55.5
67.5°	28.3
70°	18.8
72.5°	17.8
75°	15.7
77.5°	10.5
80°	7.3
82.5°	5.2
85°	3.1
87.5°	2.1
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)