

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P755931

Luminaire Tested: LD4D90BD010-EU4DR6570959040-4LBS1H

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P755931  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D90BD010-EU4DR6570959040-4LBS1H  
Description: 4 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 65° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 8385.8 lumens  
Efficiency: N/A  
Efficacy: 84.8 lumens/watt  
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96  
Luminous Opening: Circular (Dia: 0.48' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 98.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight

TEST NUMBER: P755931

CATALOG NUMBER: LD4D90BD010-EU4DR6570959040-4LBS1H

### Luminous Intensity Polar Plot





TEST NUMBER: P755931

CATALOG NUMBER: LD4D90BD010-EU4DR6570959040-4LBS1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93			93
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85			85
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78			78
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72			72
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66			66
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61			61
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56			56
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52			52
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49			49
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46			46

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	444693
5°	443572
10°	443191
15°	429531
20°	391030
25°	340760
30°	283419
35°	224567
40°	162080
45°	102394
50°	53371
55°	28368
60°	14905
65°	8195
70°	3432
75°	3791
80°	2623
85°	2278

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 102394 cd/sqm



TEST NUMBER: P755931

CATALOG NUMBER: LD4D90BD010-EU4DR6570959040-4LBS1H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	720.1	8.6
10°-20°	1971.8	23.5
20°-30°	2410.2	28.7
30°-40°	1955.6	23.3
40°-50°	974.5	11.6
50°-60°	271.8	3.2
60°-70°	61.8	0.7
70°-80°	16.1	0.2
80°-90°	4.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5102.0	60.8
0°-40°	7057.6	84.2
0°-60°	8303.9	99.0
0°-90°	8385.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8385.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	7614	
5°	7566	720
15°	7104	1972
25°	5288	2410
35°	3150	1956
45°	1240	974
55°	279	272
65°	59	62
75°	17	16
85°	3	4
90°	0	



TEST NUMBER: P755931

CATALOG NUMBER: LD4D90BD010-EU4DR6570959040-4LBS1H

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	7614.1
2.5°	7608.5
5°	7566.0
7.5°	7541.4
10°	7473.1
12.5°	7334.4
15°	7103.9
17.5°	6743.6
20°	6291.5
22.5°	5803.7
25°	5287.9
27.5°	4736.3
30°	4202.6
32.5°	3675.6
35°	3149.7
37.5°	2624.9
40°	2125.9
42.5°	1658.2
45°	1239.7
47.5°	863.8
50°	587.4
52.5°	405.0
55°	278.6
57.5°	188.0
60°	127.6
62.5°	88.4
65°	59.3
67.5°	30.2
70°	20.1
72.5°	19.0
75°	16.8
77.5°	11.2
80°	7.8
82.5°	5.6
85°	3.4
87.5°	2.2
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)