

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P755212

Luminaire Tested: LD4D85BD010-EU4DR7070959035-4LBDP1H

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P755212
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D85BD010-EU4DR7070959035-4LBDP1H
Description: 4 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8264.4 lumens
Efficiency: N/A
Efficacy: 94.2 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 87.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P755212
CATALOG NUMBER: LD4D85BD010-EU4DR7070959035-4LBDP1H

Luminous Intensity Polar Plot





TEST NUMBER: P755212

CATALOG NUMBER: LD4D85BD010-EU4DR7070959035-4LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1015196
5°	985030
10°	957577
15°	945008
20°	882441
25°	662937
30°	468634
35°	166008
40°	87289
45°	92974
50°	96276
55°	98083
60°	98684
65°	96614
70°	91173
75°	84472
80°	75002
85°	60801

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 98727 cd/sqm



TEST NUMBER: P755212

CATALOG NUMBER: LD4D85BD010-EU4DR7070959035-4LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	847.1	10.3
10°-20°	2323.6	28.1
20°-30°	2559.1	31.0
30°-40°	977.8	11.8
40°-50°	461.7	5.6
50°-60°	459.0	5.6
60°-70°	367.5	4.4
70°-80°	211.2	2.6
80°-90°	57.4	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5729.8	69.3
0°-40°	6707.6	81.2
0°-60°	7628.3	92.3
0°-90°	8264.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8264.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	9292	
5°	8981	847
15°	8354	2324
25°	5499	2559
35°	1245	978
45°	602	462
55°	515	459
65°	374	367
75°	200	211
85°	48	57
90°	0	



TEST NUMBER: P755212

CATALOG NUMBER: LD4D85BD010-EU4DR7070959035-4LBDP1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	9291.5
2.5°	9194.4
5°	8981.1
7.5°	8803.1
10°	8631.0
12.5°	8485.3
15°	8354.4
17.5°	8038.1
20°	7589.4
22.5°	6621.4
25°	5499.0
27.5°	4787.0
30°	3714.5
32.5°	2399.4
35°	1244.6
37.5°	672.3
40°	612.0
42.5°	607.6
45°	601.7
47.5°	588.4
50°	566.4
52.5°	541.4
55°	514.9
57.5°	485.5
60°	451.6
62.5°	413.4
65°	373.7
67.5°	329.5
70°	285.4
72.5°	241.3
75°	200.1
77.5°	157.4
80°	119.2
82.5°	83.9
85°	48.5
87.5°	19.1
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)