

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P756006

Luminaire Tested: LD4D90BD010-EU4DR7070959040-4LBDP1LI

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P756006
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D90BD010-EU4DR7070959040-4LBDP1LI
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9636.0 lumens
Efficiency: N/A
Efficacy: 97.4 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 98.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P756006
CATALOG NUMBER: LD4D90BD010-EU4DR7070959040-4LBDP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P756006

CATALOG NUMBER: LD4D90BD010-EU4DR7070959040-4LBDP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1183698
5°	1148527
10°	1116508
15°	1101865
20°	1028910
25°	772968
30°	546427
35°	193552
40°	101781
45°	108394
50°	112255
55°	114351
60°	115073
65°	112643
70°	106315
75°	98488
80°	87397
85°	70955

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 115097 cd/sqm



TEST NUMBER: P756006

CATALOG NUMBER: LD4D90BD010-EU4DR7070959040-4LBDP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	987.7	10.3
10°-20°	2709.3	28.1
20°-30°	2983.9	31.0
30°-40°	1140.1	11.8
40°-50°	538.3	5.6
50°-60°	535.1	5.6
60°-70°	428.5	4.4
70°-80°	246.3	2.6
80°-90°	67.0	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6680.8	69.3
0°-40°	7820.9	81.2
0°-60°	8894.3	92.3
0°-90°	9636.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	9636.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	10834	
5°	10472	988
15°	9741	2709
25°	6412	2984
35°	1451	1140
45°	702	538
55°	600	535
65°	436	428
75°	233	246
85°	57	67
90°	0	



TEST NUMBER: P756006

CATALOG NUMBER: LD4D90BD010-EU4DR7070959040-4LBDP1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	10833.7
2.5°	10720.5
5°	10471.8
7.5°	10264.2
10°	10063.5
12.5°	9893.7
15°	9741.1
17.5°	9372.3
20°	8849.1
22.5°	7720.5
25°	6411.7
27.5°	5581.5
30°	4331.1
32.5°	2797.6
35°	1451.1
37.5°	783.9
40°	713.6
42.5°	708.4
45°	701.5
47.5°	686.1
50°	660.4
52.5°	631.2
55°	600.3
57.5°	566.0
60°	526.6
62.5°	482.0
65°	435.7
67.5°	384.2
70°	332.8
72.5°	281.3
75°	233.3
77.5°	183.5
80°	138.9
82.5°	97.8
85°	56.6
87.5°	22.3
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)