

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P755946

Luminaire Tested: LD4D90BD010-EU4DR6570959050-4LBS1MW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P755946
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D90BD010-EU4DR6570959050-4LBS1MW
Description: 4 INCH ROUND SHALLOW MATTE WHITE TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8025.4 lumens
Efficiency: N/A
Efficacy: 81.1 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct

Input Watts (W): 98.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P755946

CATALOG NUMBER: LD4D90BD010-EU4DR6570959050-4LBS1MW

Luminous Intensity Polar Plot





TEST NUMBER: P755946

CATALOG NUMBER: LD4D90BD010-EU4DR6570959050-4LBS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93																			
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85																			
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78																			
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72																			
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66																			
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61																			
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56																			
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52																			
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49																			
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	425577
5°	424500
10°	424136
15°	411065
20°	374224
25°	326113
30°	271233
35°	214913
40°	155112
45°	97991
50°	51082
55°	27146
60°	14262
65°	7849
70°	3296
75°	3633
80°	2523
85°	2144

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 97991 cd/sqm



TEST NUMBER: P755946

CATALOG NUMBER: LD4D90BD010-EU4DR6570959050-4LBS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	689.1	8.6
10°-20°	1887.0	23.5
20°-30°	2306.6	28.7
30°-40°	1871.5	23.3
40°-50°	932.6	11.6
50°-60°	260.1	3.2
60°-70°	59.1	0.7
70°-80°	15.4	0.2
80°-90°	3.9	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4882.7	60.8
0°-40°	6754.2	84.2
0°-60°	7946.9	99.0
0°-90°	8025.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8025.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7287	
5°	7241	689
15°	6798	1887
25°	5061	2307
35°	3014	1871
45°	1186	933
55°	267	260
65°	57	59
75°	16	15
85°	3	4
90°	0	



TEST NUMBER: P755946

CATALOG NUMBER: LD4D90BD010-EU4DR6570959050-4LBS1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	7286.8
2.5°	7281.4
5°	7240.7
7.5°	7217.2
10°	7151.8
12.5°	7019.1
15°	6798.5
17.5°	6453.7
20°	6021.1
22.5°	5554.2
25°	5060.6
27.5°	4532.7
30°	4021.9
32.5°	3517.6
35°	3014.3
37.5°	2512.1
40°	2034.5
42.5°	1586.9
45°	1186.4
47.5°	826.7
50°	562.2
52.5°	387.6
55°	266.6
57.5°	179.9
60°	122.1
62.5°	84.6
65°	56.8
67.5°	28.9
70°	19.3
72.5°	18.2
75°	16.1
77.5°	10.7
80°	7.5
82.5°	5.4
85°	3.2
87.5°	2.1
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)