

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P756019

Luminaire Tested: LD4D90BD010-EU4DR7070959050-4LBDP1LI

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P756019  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D90BD010-EU4DR7070959050-4LBDP1LI  
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 70° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 9704.9 lumens  
Efficiency: N/A  
Efficacy: 98.1 lumens/watt  
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct


Input Watts (W): 98.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



Downlight

TEST NUMBER: P756019  
CATALOG NUMBER: LD4D90BD010-EU4DR7070959050-4LBDP1LI

### Luminous Intensity Polar Plot





TEST NUMBER: P756019

CATALOG NUMBER: LD4D90BD010-EU4DR7070959050-4LBDP1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91		
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83		
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76		
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70		
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65		
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61		
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57		
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53		
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50		
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48		

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1192155
5°	1156731
10°	1124485
15°	1109727
20°	1036259
25°	778490
30°	550325
35°	194939
40°	102508
45°	109182
50°	113053
55°	115170
60°	115904
65°	113444
70°	107050
75°	99163
80°	88026
85°	71457

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 57.5°  
 Luminance: 115931 cd/sqm



TEST NUMBER: P756019

CATALOG NUMBER: LD4D90BD010-EU4DR7070959050-4LBDP1LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	994.8	10.3
10°-20°	2728.6	28.1
20°-30°	3005.2	31.0
30°-40°	1148.2	11.8
40°-50°	542.2	5.6
50°-60°	539.0	5.6
60°-70°	431.5	4.4
70°-80°	248.0	2.6
80°-90°	67.4	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6728.5	69.3
0°-40°	7876.8	81.2
0°-60°	8957.9	92.3
0°-90°	9704.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	9704.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	10911	
5°	10547	995
15°	9811	2729
25°	6458	3005
35°	1462	1148
45°	707	542
55°	605	539
65°	439	432
75°	235	248
85°	57	67
90°	0	



TEST NUMBER: P756019

CATALOG NUMBER: LD4D90BD010-EU4DR7070959050-4LBDP1LI

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	10911.1
2.5°	10797.1
5°	10546.6
7.5°	10337.5
10°	10135.4
12.5°	9964.4
15°	9810.6
17.5°	9439.2
20°	8912.3
22.5°	7775.6
25°	6457.5
27.5°	5621.4
30°	4362.0
32.5°	2817.6
35°	1461.5
37.5°	789.5
40°	718.7
42.5°	713.5
45°	706.6
47.5°	691.0
50°	665.1
52.5°	635.7
55°	604.6
57.5°	570.1
60°	530.4
62.5°	485.4
65°	438.8
67.5°	387.0
70°	335.1
72.5°	283.3
75°	234.9
77.5°	184.8
80°	139.9
82.5°	98.5
85°	57.0
87.5°	22.5
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)