

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P755070

Luminaire Tested: LD4D85BD010-EU4DR6070959040-4LBDP1LI

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P755070  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D85BD010-EU4DR6070959040-4LBDP1LI  
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 60° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 9024.1 lumens  
Efficiency: N/A  
Efficacy: 102.9 lumens/watt  
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct


Input Watts (W): 87.7  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



Downlight

TEST NUMBER: P755070  
CATALOG NUMBER: LD4D85BD010-EU4DR6070959040-4LBDP1LI

### Luminous Intensity Polar Plot





TEST NUMBER: P755070

CATALOG NUMBER: LD4D85BD010-EU4DR6070959040-4LBDP1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93		
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86		
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80		
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75		
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70		
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66		
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62		
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59		
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55		
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53		

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1170969
5°	1199769
10°	1214252
15°	1156749
20°	1019887
25°	824916
30°	557983
35°	279610
40°	45356
45°	44393
50°	45283
55°	45965
60°	47244
65°	48320
70°	49452
75°	50067
80°	48260
85°	40241

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 75°  
 Luminance: 50067 cd/sqm



TEST NUMBER: P755070

CATALOG NUMBER: LD4D85BD010-EU4DR6070959040-4LBDP1LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	1045.5	11.6
10°-20°	2828.6	31.3
20°-30°	3043.4	33.7
30°-40°	1322.9	14.7
40°-50°	222.2	2.5
50°-60°	216.0	2.4
60°-70°	184.8	2.0
70°-80°	123.6	1.4
80°-90°	37.0	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6917.5	76.7
0°-40°	8240.4	91.3
0°-60°	8678.6	96.2
0°-90°	9024.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	9024.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	10717	
5°	10939	###
15°	10226	2829
25°	6843	3043
35°	2096	1323
45°	287	222
55°	241	216
65°	187	185
75°	119	124
85°	32	37
90°	0	



TEST NUMBER: P755070

CATALOG NUMBER: LD4D85BD010-EU4DR6070959040-4LBDP1LI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	10717.2
2.5°	11018.5
5°	10939.0
7.5°	10964.1
10°	10944.5
12.5°	10718.6
15°	10226.3
17.5°	9565.1
20°	8771.5
22.5°	7922.1
25°	6842.6
27.5°	5473.0
30°	4422.7
32.5°	3408.8
35°	2096.3
37.5°	896.8
40°	318.0
42.5°	292.9
45°	287.3
47.5°	277.6
50°	266.4
52.5°	253.8
55°	241.3
57.5°	228.7
60°	216.2
62.5°	202.2
65°	186.9
67.5°	171.6
70°	154.8
72.5°	136.7
75°	118.6
77.5°	97.6
80°	76.7
82.5°	54.4
85°	32.1
87.5°	11.2
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)