

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P755148

Luminaire Tested: LD4D85BD010-EU4DR6570959040-4LBDP1LI

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P755148
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D85BD010-EU4DR6570959040-4LBDP1LI
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7885.0 lumens
Efficiency: N/A
Efficacy: 89.9 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 87.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P755148

CATALOG NUMBER: LD4D85BD010-EU4DR6570959040-4LBDP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P755148

CATALOG NUMBER: LD4D85BD010-EU4DR6570959040-4LBDP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93																			
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87																			
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80																			
4	97	89	84	79	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	83	78	73	90	83	77	73	81	76	72	79	75	72	77	74	71	69																			
6	87	78	72	68	86	77	72	68	76	71	67	74	70	67	73	69	66	65																			
7	83	73	67	63	81	73	67	63	71	66	62	70	66	62	69	65	62	60																			
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	57																			
9	75	65	59	55	74	65	59	55	64	58	55	63	58	55	62	58	54	53																			
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	848224
5°	848920
10°	878805
15°	880261
20°	810434
25°	690532
30°	528625
35°	373458
40°	220449
45°	89497
50°	32449
55°	18078
60°	10358
65°	5714
70°	6006
75°	4644
80°	4845
85°	4137

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 89497 cd/sqm



TEST NUMBER: P755148

CATALOG NUMBER: LD4D85BD010-EU4DR6570959040-4LBDP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	747.5	9.5
10°-20°	2156.3	27.3
20°-30°	2587.2	32.8
30°-40°	1738.6	22.1
40°-50°	520.5	6.6
50°-60°	91.9	1.2
60°-70°	26.1	0.3
70°-80°	12.8	0.2
80°-90°	4.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5491.0	69.6
0°-40°	7229.7	91.7
0°-60°	7842.0	99.5
0°-90°	7885.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7885.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7763	
5°	7740	748
15°	7782	2156
25°	5728	2587
35°	2800	1739
45°	579	520
55°	95	92
65°	22	26
75°	11	13
85°	3	4
90°	0	



TEST NUMBER: P755148

CATALOG NUMBER: LD4D85BD010-EU4DR6570959040-4LBDP1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	7763.3
2.5°	7796.4
5°	7740.1
7.5°	7857.1
10°	7921.0
12.5°	7905.6
15°	7782.0
17.5°	7479.8
20°	6970.1
22.5°	6369.9
25°	5727.9
27.5°	5003.1
30°	4190.0
32.5°	3453.0
35°	2799.9
37.5°	2154.6
40°	1545.6
42.5°	1009.4
45°	579.2
47.5°	306.7
50°	190.9
52.5°	132.4
55°	94.9
57.5°	68.4
60°	47.4
62.5°	30.9
65°	22.1
67.5°	19.9
70°	18.8
72.5°	14.3
75°	11.0
77.5°	9.9
80°	7.7
82.5°	5.5
85°	3.3
87.5°	2.2
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)