

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P755006

Luminaire Tested: LD4D85BD010-EU4DR5570959050-4LBDP1MW

Issue Date: 1/30/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P755006  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-52)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 1/30/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D85BD010-EU4DR5570959050-4LBDP1MW  
Description: 4 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 55° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 8079.8 lumens  
Efficiency: N/A  
Efficacy: 92.1 lumens/watt  
Spacing Criteria (0/90/45): 0.89 / 0.89 / 0.87  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct


Input Watts (W): 87.7  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



Downlight

TEST NUMBER: P755006  
CATALOG NUMBER: LD4D85BD010-EU4DR5570959050-4LBDP1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P755006

CATALOG NUMBER: LD4D85BD010-EU4DR5570959050-4LBDP1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20																	
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR																																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																											
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94																											
2	108	103	99	96	106	101	98	95	98	95	92	95	93	90	92	90	89	87																											
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81																											
4	97	90	84	80	95	88	83	79	86	82	78	84	81	78	82	79	77	75																											
5	92	84	78	74	91	83	77	73	81	76	73	79	75	72	78	74	71	70																											
6	88	79	73	68	86	78	72	68	76	71	68	75	70	67	74	70	67	65																											
7	83	74	68	64	82	73	67	63	72	67	63	71	66	63	70	65	62	61																											
8	79	69	63	59	78	69	63	59	68	63	59	67	62	59	66	62	58	57																											
9	75	66	60	56	74	65	59	55	64	59	55	63	58	55	62	58	55	54																											
10	72	62	56	52	71	61	56	52	61	56	52	60	55	52	59	55	52	50																											

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	989924
5°	950613
10°	947026
15°	919829
20°	824758
25°	681611
30°	514873
35°	373325
40°	238919
45°	109121
50°	35679
55°	15392
60°	6621
65°	879
70°	0
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 109121 cd/sqm



TEST NUMBER: P755006

CATALOG NUMBER: LD4D85BD010-EU4DR5570959050-4LBDP1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	824.7	10.2
10°-20°	2250.9	27.9
20°-30°	2565.1	31.7
30°-40°	1746.2	21.6
40°-50°	601.7	7.4
50°-60°	83.1	1.0
60°-70°	8.0	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5640.7	69.8
0°-40°	7386.9	91.4
0°-60°	8071.7	99.9
0°-90°	8079.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8079.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	9060	
5°	8667	825
15°	8132	2251
25°	5654	2565
35°	2799	1746
45°	706	602
55°	81	83
65°	3	8
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P755006

CATALOG NUMBER: LD4D85BD010-EU4DR5570959050-4LBDP1MW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	9060.2
2.5°	8852.5
5°	8667.3
7.5°	8576.3
10°	8535.9
12.5°	8401.2
15°	8131.8
17.5°	7704.0
20°	7093.3
22.5°	6388.2
25°	5653.9
27.5°	4889.4
30°	4081.0
32.5°	3396.2
35°	2798.9
37.5°	2230.8
40°	1675.1
42.5°	1160.9
45°	706.2
47.5°	380.6
50°	209.9
52.5°	124.6
55°	80.8
57.5°	51.6
60°	30.3
62.5°	13.5
65°	3.4
67.5°	1.1
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)