

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P755952

Luminaire Tested: LD4D90BD010-EU4DR7070959024-4LBDP1B

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P755952  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D90BD010-EU4DR7070959024-4LBDP1B  
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 70° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4325.5 lumens  
Efficiency: N/A  
Efficacy: 43.7 lumens/watt  
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct


Input Watts (W): 98.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



Downlight

TEST NUMBER: P755952  
CATALOG NUMBER: LD4D90BD010-EU4DR7070959024-4LBDP1B

### Luminous Intensity Polar Plot





TEST NUMBER: P755952

CATALOG NUMBER: LD4D90BD010-EU4DR7070959024-4LBDP1B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	531335
5°	515553
10°	501178
15°	494607
20°	461859
25°	346972
30°	245274
35°	86886
40°	45684
45°	48658
50°	50382
55°	51337
60°	51658
65°	50569
70°	47727
75°	44199
80°	39263
85°	31842

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 57.5°  
 Luminance: 51672 cd/sqm



TEST NUMBER: P755952

CATALOG NUMBER: LD4D90BD010-EU4DR7070959024-4LBDP1B

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	443.4	10.3
10°-20°	1216.1	28.1
20°-30°	1339.4	31.0
30°-40°	511.8	11.8
40°-50°	241.6	5.6
50°-60°	240.2	5.6
60°-70°	192.4	4.4
70°-80°	110.6	2.6
80°-90°	30.1	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2998.9	69.3
0°-40°	3510.6	81.2
0°-60°	3992.5	92.3
0°-90°	4325.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4325.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4863	
5°	4701	443
15°	4373	1216
25°	2878	1339
35°	651	512
45°	315	242
55°	270	240
65°	196	192
75°	105	111
85°	25	30
90°	0	



TEST NUMBER: P755952

CATALOG NUMBER: LD4D90BD010-EU4DR7070959024-4LBDP1B

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	4863.0
2.5°	4812.2
5°	4700.6
7.5°	4607.4
10°	4517.3
12.5°	4441.1
15°	4372.6
17.5°	4207.0
20°	3972.2
22.5°	3465.6
25°	2878.1
27.5°	2505.4
30°	1944.1
32.5°	1255.8
35°	651.4
37.5°	351.9
40°	320.3
42.5°	318.0
45°	314.9
47.5°	308.0
50°	296.4
52.5°	283.3
55°	269.5
57.5°	254.1
60°	236.4
62.5°	216.4
65°	195.6
67.5°	172.5
70°	149.4
72.5°	126.3
75°	104.7
77.5°	82.4
80°	62.4
82.5°	43.9
85°	25.4
87.5°	10.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)