

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P742150

Luminaire Tested: LD4D10D010-EU4DR300210IC9040-4LBCSSQMMS

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P742150
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D10D010-EU4DR300210IC9040-4LBCSSQMMS
Description: 4 INCH SQAURE SHALLOW CAST MATTE METALLIC SILVER TRIM, WITH 30° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 966.8 lumens
Efficiency: N/A
Efficacy: 82.6 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.49
Luminous Opening: Rectangular (W 0.38' x L: 0.38' x H: 0')
CIE Type: Direct

Input Watts (W): 11.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P742150
CATALOG NUMBER: LD4D10D010-EU4DR300210IC9040-4LBCSSQMMS

Luminous Intensity Polar Plot





TEST NUMBER: P742150

CATALOG NUMBER: LD4D10D010-EU4DR300210IC9040-4LBCSSQMMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96																			
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92																			
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89																			
4	103	98	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85																			
5	100	94	89	86	98	93	89	86	91	88	85	90	86	84	88	86	83	82																			
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79																			
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77																			
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74																			
9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73	72																			
10	85	78	74	71	85	78	74	71	77	73	71	76	73	71	76	73	70	69																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	237958	237958	237958
5°	231122	230861	231137
10°	200186	198780	200140
15°	130617	129912	129262
20°	64945	67388	64863
25°	32718	36891	32051
30°	13099	14274	11410
35°	6074	5821	4878
40°	2618	2918	2478
45°	1851	2295	1862
50°	631	1667	679
55°	374	694	387
60°	260	306	260
65°	163	163	163
70°	112	67	112
75°	0	59	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°
 Vertical Angle: 45°
 Luminance: 2295 cd/sqm



TEST NUMBER: P742150
 CATALOG NUMBER: LD4D10D010-EU4DR300210IC9040-4LBCSSQMMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	273.4	28.3
10°-20°	440.3	45.5
20°-30°	190.2	19.7
30°-40°	43.4	4.5
40°-50°	14.9	1.5
50°-60°	3.6	0.4
60°-70°	0.9	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	903.9	93.5
0°-40°	947.2	98.0
0°-60°	965.8	99.9
0°-90°	966.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	966.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3109	3109	3109	3109	3109	
5°	3008	3005	3005	3011	3008	274
15°	1648	1628	1639	1634	1631	441
25°	387	402	437	392	380	185
35°	65	66	62	62	52	44
45°	17	21	21	21	17	12
55°	3	3	5	3	3	3
65°	1	1	1	1	1	1
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	



TEST NUMBER: P742150

CATALOG NUMBER: LD4D10D010-EU4DR300210IC9040-4LBCSSQMMS

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3108.8	3108.8	3108.8	3108.8	3108.8
2.5°	3088.2	3086.0	3087.3	3088.8	3089.4
5°	3008.0	3005.1	3004.6	3010.8	3008.2
7.5°	2846.4	2842.3	2836.0	2850.2	2863.5
10°	2575.6	2571.1	2557.5	2564.2	2575.0
12.5°	2175.9	2161.1	2160.8	2182.1	2179.3
15°	1648.3	1628.4	1639.4	1634.1	1631.2
17.5°	1108.4	1100.8	1115.4	1111.0	1091.9
20°	797.3	799.3	827.3	813.2	796.3
22.5°	581.8	589.0	622.1	586.0	572.7
25°	387.4	402.0	436.8	391.8	379.5
27.5°	238.2	245.0	280.2	235.2	228.5
30°	148.2	144.8	161.5	138.6	129.1
32.5°	97.2	92.9	98.3	88.2	80.6
35°	65.0	66.4	62.3	61.8	52.2
37.5°	40.6	46.7	41.2	43.9	33.6
40°	26.2	33.9	29.2	32.2	24.8
42.5°	21.5	26.1	23.9	25.5	22.0
45°	17.1	21.2	21.2	21.2	17.2
47.5°	9.5	14.2	18.2	14.5	10.1
50°	5.3	7.2	14.0	7.5	5.7
52.5°	3.7	4.1	9.6	4.3	3.8
55°	2.8	2.9	5.2	3.0	2.9
57.5°	2.1	2.3	2.8	2.3	2.1
60°	1.7	1.7	2.0	1.8	1.7
62.5°	1.2	1.2	1.4	1.2	1.2
65°	0.9	0.9	0.9	0.9	0.9
67.5°	0.5	0.6	0.6	0.6	0.6
70°	0.5	0.3	0.3	0.3	0.5
72.5°	0.3	0.2	0.2	0.2	0.2
75°	0.0	0.0	0.2	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - 90°-270°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)