

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P742889

Luminaire Tested: LD4D15D010-EU4DR1515309027-4LBCSSQMMS

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P742889
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-21)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D15D010-EU4DR1515309027-4LBCSSQMMS
Description: 4 INCH SQAURE SHALLOW CAST MATTE METALLIC SILVER TRIM, WITH 15° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1202.7 lumens
Efficiency: N/A
Efficacy: 76.1 lumens/watt
Spacing Criteria (0/90/45): 0.22 / 0.22 / 0.23
Luminous Opening: Vertical Cylinder (Dia: 0.35' x H: 0.35')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P742889
CATALOG NUMBER: LD4D15D010-EU4DR1515309027-4LBCSSQMMS

Luminous Intensity Polar Plot





TEST NUMBER: P742889

CATALOG NUMBER: LD4D15D010-EU4DR1515309027-4LBCSSQMMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						100													
1	116	114	112	111	113	112	110	109	108	107	106	104	103	103	101	100	100	98						98													
2	113	110	107	105	111	108	106	104	105	103	102	102	101	100	100	98	98	96						96													
3	110	106	103	101	108	105	102	100	103	100	99	100	99	97	98	97	96	94						94													
4	108	103	100	98	106	102	99	97	100	98	96	99	97	95	97	95	94	93						93													
5	106	101	98	95	104	100	97	95	98	96	94	97	95	93	96	94	92	92						92													
6	104	99	95	93	102	98	95	93	97	94	92	96	93	92	95	93	91	90						90													
7	102	97	94	91	101	96	93	91	95	93	91	94	92	90	93	91	90	89						89													
8	100	95	92	90	99	95	92	90	94	91	89	93	91	89	92	90	89	88						88													
9	99	93	90	88	98	93	90	88	92	90	88	92	89	88	91	89	87	87						87													
10	97	92	89	87	96	92	89	87	91	89	87	91	88	87	90	88	86	86						86													

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1843786	1843786	1843786
5°	1083496	1069461	1077927
10°	323376	325634	330626
15°	80438	82002	79474
20°	24064	27869	24580
25°	8483	10805	8592
30°	3115	4103	3167
35°	1561	1765	1510
40°	987	1087	987
45°	728	777	728
50°	577	577	577
55°	480	480	480
60°	386	386	386
65°	300	300	300
70°	256	256	256
75°	159	159	212
80°	110	110	110
85°	58	58	58

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°

Vertical Angle: 45°

Luminance: 777 cd/sqm



TEST NUMBER: P742889

CATALOG NUMBER: LD4D15D010-EU4DR1515309027-4LBCSSQMMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	780.0	64.9
10°-20°	320.8	26.7
20°-30°	63.7	5.3
30°-40°	15.9	1.3
40°-50°	8.4	0.7
50°-60°	6.2	0.5
60°-70°	4.4	0.4
70°-80°	2.5	0.2
80°-90°	0.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1164.6	96.8
0°-40°	1180.5	98.2
0°-60°	1195.0	99.4
0°-90°	1202.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1202.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	16386	16386	16386	16386	16386	
5°	10661	10552	10523	10596	10606	779
15°	926	943	944	928	915	318
25°	109	124	139	123	110	57
35°	22	23	24	23	21	15
45°	10	10	11	10	10	8
55°	7	7	7	7	7	6
65°	4	4	4	4	4	4
75°	2	2	2	2	3	2
85°	1	1	1	1	1	1
90°	0	0	0	0	0	



TEST NUMBER: P742889

CATALOG NUMBER: LD4D15D010-EU4DR1515309027-4LBCSSQMMS

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	16386.3	16386.3	16386.3	16386.3	16386.3
2.5°	14781.1	14793.6	14798.4	14813.0	14867.1
5°	10661.3	10551.7	10523.2	10596.1	10606.5
7.5°	6315.3	6337.5	6418.7	6436.7	6371.5
10°	3465.7	3494.1	3489.9	3514.9	3543.4
12.5°	1772.4	1750.2	1743.2	1771.7	1732.1
15°	926.1	943.4	944.1	927.5	915.0
17.5°	498.1	518.2	551.5	524.4	482.8
20°	294.1	312.2	340.6	318.4	300.4
22.5°	181.7	196.3	216.4	199.1	184.5
25°	108.9	123.5	138.7	122.8	110.3
27.5°	64.5	77.0	86.7	76.3	63.8
30°	41.6	48.6	54.8	47.9	42.3
32.5°	29.1	31.9	34.7	31.9	29.1
35°	21.5	22.9	24.3	22.9	20.8
37.5°	16.6	18.0	18.7	17.3	16.0
40°	13.9	14.6	15.3	14.6	13.9
42.5°	11.8	12.5	12.5	12.5	11.8
45°	10.4	10.4	11.1	10.4	10.4
47.5°	9.0	9.0	9.7	9.0	9.0
50°	8.3	8.3	8.3	8.3	8.3
52.5°	7.6	7.6	7.6	7.6	7.6
55°	6.9	6.9	6.9	6.9	6.9
57.5°	6.2	6.2	6.2	6.2	6.2
60°	5.5	5.5	5.5	5.5	5.5
62.5°	4.9	4.9	4.9	4.9	4.9
65°	4.2	4.2	4.2	4.2	4.2
67.5°	4.2	4.2	4.2	4.2	4.2
70°	3.5	3.5	3.5	3.5	3.5
72.5°	2.8	2.8	2.8	2.8	2.8
75°	2.1	2.1	2.1	2.1	2.8
77.5°	2.1	2.1	2.1	2.1	2.1
80°	1.4	1.4	1.4	1.4	1.4
82.5°	1.4	1.4	1.4	1.4	1.4
85°	0.7	0.7	0.7	0.7	0.7
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - - 90°-270°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)