

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P755850

Luminaire Tested: LD4D90BD010-EU4DR6070959040-4LBDP1LI

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P755850
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D90BD010-EU4DR6070959040-4LBDP1LI
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9573.3 lumens
Efficiency: N/A
Efficacy: 96.8 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 98.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P755850
CATALOG NUMBER: LD4D90BD010-EU4DR6070959040-4LBDP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P755850

CATALOG NUMBER: LD4D90BD010-EU4DR6070959040-4LBDP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93																			
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86																			
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80																			
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70																			
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66																			
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62																			
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59																			
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55																			
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1242240
5°	1272782
10°	1288164
15°	1227140
20°	1081966
25°	875127
30°	591946
35°	296630
40°	48123
45°	47097
50°	48036
55°	48766
60°	50107
65°	51267
70°	52455
75°	53107
80°	51217
85°	42623

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 75°
 Luminance: 53107 cd/sqm



TEST NUMBER: P755850

CATALOG NUMBER: LD4D90BD010-EU4DR6070959040-4LBDP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1109.1	11.6
10°-20°	3000.8	31.3
20°-30°	3228.6	33.7
30°-40°	1403.4	14.7
40°-50°	235.7	2.5
50°-60°	229.2	2.4
60°-70°	196.0	2.0
70°-80°	131.2	1.4
80°-90°	39.2	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	7338.5	76.7
0°-40°	8742.0	91.3
0°-60°	9206.9	96.2
0°-90°	9573.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	9573.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	11370	
5°	11605	###
15°	10849	3001
25°	7259	3229
35°	2224	1403
45°	305	236
55°	256	229
65°	198	196
75°	126	131
85°	34	39
90°	0	



TEST NUMBER: P755850

CATALOG NUMBER: LD4D90BD010-EU4DR6070959040-4LBDP1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	11369.5
2.5°	11689.1
5°	11604.7
7.5°	11631.4
10°	11610.7
12.5°	11371.0
15°	10848.6
17.5°	10147.3
20°	9305.4
22.5°	8404.3
25°	7259.1
27.5°	5806.1
30°	4691.9
32.5°	3616.2
35°	2223.9
37.5°	951.4
40°	337.4
42.5°	310.7
45°	304.8
47.5°	294.4
50°	282.6
52.5°	269.3
55°	256.0
57.5°	242.7
60°	229.3
62.5°	214.5
65°	198.3
67.5°	182.0
70°	164.2
72.5°	145.0
75°	125.8
77.5°	103.6
80°	81.4
82.5°	57.7
85°	34.0
87.5°	11.8
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)