

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P756007

Luminaire Tested: LD4D90BD010-EU4DR7070959040-4LBDP1MW

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P756007
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D90BD010-EU4DR7070959040-4LBDP1MW
Description: 4 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7168.2 lumens
Efficiency: N/A
Efficacy: 72.5 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 98.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P756007
CATALOG NUMBER: LD4D90BD010-EU4DR7070959040-4LBDP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P756007
 CATALOG NUMBER: LD4D90BD010-EU4DR7070959040-4LBDP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	880554
5°	854382
10°	830577
15°	819677
20°	765401
25°	575015
30°	406486
35°	143987
40°	75708
45°	80643
50°	83511
55°	85073
60°	85595
65°	83791
70°	79066
75°	73243
80°	65060
85°	52778

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 85631 cd/sqm



TEST NUMBER: P756007

CATALOG NUMBER: LD4D90BD010-EU4DR7070959040-4LBDP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	734.8	10.3
10°-20°	2015.4	28.1
20°-30°	2219.7	31.0
30°-40°	848.1	11.8
40°-50°	400.5	5.6
50°-60°	398.1	5.6
60°-70°	318.7	4.4
70°-80°	183.2	2.6
80°-90°	49.8	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4969.9	69.3
0°-40°	5817.9	81.2
0°-60°	6616.5	92.3
0°-90°	7168.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7168.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8059	
5°	7790	735
15°	7246	2015
25°	4770	2220
35°	1080	848
45°	522	400
55°	447	398
65°	324	319
75°	174	183
85°	42	50
90°	0	



TEST NUMBER: P756007

CATALOG NUMBER: LD4D90BD010-EU4DR7070959040-4LBDP1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	8059.2
2.5°	7975.0
5°	7789.9
7.5°	7635.5
10°	7486.3
12.5°	7359.9
15°	7246.4
17.5°	6972.0
20°	6582.8
22.5°	5743.2
25°	4769.7
27.5°	4152.1
30°	3221.9
32.5°	2081.1
35°	1079.5
37.5°	583.1
40°	530.8
42.5°	527.0
45°	521.9
47.5°	510.4
50°	491.3
52.5°	469.6
55°	446.6
57.5°	421.1
60°	391.7
62.5°	358.6
65°	324.1
67.5°	285.8
70°	247.5
72.5°	209.3
75°	173.5
77.5°	136.5
80°	103.4
82.5°	72.7
85°	42.1
87.5°	16.6
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)