

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P755862

Luminaire Tested: LD4D90BD010-EU4DR6070959050-4LBDP1H

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P755862
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D90BD010-EU4DR6070959050-4LBDP1H
Description: 4 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9182.6 lumens
Efficiency: N/A
Efficacy: 92.8 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 98.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P755862
CATALOG NUMBER: LD4D90BD010-EU4DR6070959050-4LBDP1H

Luminous Intensity Polar Plot





TEST NUMBER: P755862

CATALOG NUMBER: LD4D90BD010-EU4DR6070959050-4LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93																			
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86																			
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80																			
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70																			
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66																			
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62																			
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59																			
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55																			
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1191532
5°	1220838
10°	1235575
15°	1177053
20°	1037805
25°	839407
30°	567786
35°	284519
40°	46155
45°	45181
50°	46081
55°	46765
60°	48075
65°	49173
70°	50314
75°	50911
80°	49141
85°	40868

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 75°
 Luminance: 50911 cd/sqm



TEST NUMBER: P755862

CATALOG NUMBER: LD4D90BD010-EU4DR6070959050-4LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1063.8	11.6
10°-20°	2878.3	31.3
20°-30°	3096.8	33.7
30°-40°	1346.1	14.7
40°-50°	226.1	2.5
50°-60°	219.8	2.4
60°-70°	188.0	2.0
70°-80°	125.8	1.4
80°-90°	37.7	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	7039.0	76.7
0°-40°	8385.1	91.3
0°-60°	8831.1	96.2
0°-90°	9182.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	9182.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	10905	
5°	11131	###
15°	10406	2878
25°	6963	3097
35°	2133	1346
45°	292	226
55°	246	220
65°	190	188
75°	121	126
85°	33	38
90°	0	



TEST NUMBER: P755862

CATALOG NUMBER: LD4D90BD010-EU4DR6070959050-4LBDP1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	10905.4
2.5°	11212.0
5°	11131.1
7.5°	11156.6
10°	11136.7
12.5°	10906.8
15°	10405.8
17.5°	9733.1
20°	8925.6
22.5°	8061.3
25°	6962.8
27.5°	5569.1
30°	4500.4
32.5°	3468.6
35°	2133.1
37.5°	912.6
40°	323.6
42.5°	298.0
45°	292.4
47.5°	282.4
50°	271.1
52.5°	258.3
55°	245.5
57.5°	232.8
60°	220.0
62.5°	205.8
65°	190.2
67.5°	174.6
70°	157.5
72.5°	139.1
75°	120.6
77.5°	99.3
80°	78.1
82.5°	55.4
85°	32.6
87.5°	11.4
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)