

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P743767

Luminaire Tested: LD4D15D010-EU4DR700215IC9040-4LBSQW1MW

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P743767
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D15D010-EU4DR700215IC9040-4LBSQW1MW
Description: 4 INCH SQAURE DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1209.7 lumens
Efficiency: N/A
Efficacy: 76.6 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P743767

CATALOG NUMBER: LD4D15D010-EU4DR700215IC9040-4LBSQW1MW

Luminous Intensity Polar Plot





TEST NUMBER: P743767

CATALOG NUMBER: LD4D15D010-EU4DR700215IC9040-4LBSQW1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	88	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	148606
5°	144194
10°	140170
15°	138340
20°	129179
25°	97035
30°	68595
35°	24302
40°	12780
45°	13613
50°	14091
55°	14344
60°	14444
65°	14142
70°	13353
75°	12369
80°	10948
85°	8901

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 60°
 Luminance: 14444 cd/sqm



TEST NUMBER: P743767

CATALOG NUMBER: LD4D15D010-EU4DR700215IC9040-4LBSQW1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	124.0	10.3
10°-20°	340.1	28.1
20°-30°	374.6	31.0
30°-40°	143.1	11.8
40°-50°	67.6	5.6
50°-60°	67.1	5.6
60°-70°	53.8	4.4
70°-80°	30.9	2.6
80°-90°	8.4	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	838.7	69.3
0°-40°	981.9	81.2
0°-60°	1116.6	92.3
0°-90°	1209.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1209.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1360	
5°	1315	124
15°	1223	340
25°	805	375
35°	182	143
45°	88	68
55°	75	67
65°	55	54
75°	29	31
85°	7	8
90°	0	



TEST NUMBER: P743767

CATALOG NUMBER: LD4D15D010-EU4DR700215IC9040-4LBSQW1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1360.1
2.5°	1345.9
5°	1314.7
7.5°	1288.6
10°	1263.4
12.5°	1242.1
15°	1223.0
17.5°	1176.7
20°	1111.0
22.5°	969.3
25°	804.9
27.5°	700.7
30°	543.7
32.5°	351.2
35°	182.2
37.5°	98.4
40°	89.6
42.5°	88.9
45°	88.1
47.5°	86.1
50°	82.9
52.5°	79.2
55°	75.3
57.5°	71.0
60°	66.1
62.5°	60.5
65°	54.7
67.5°	48.2
70°	41.8
72.5°	35.3
75°	29.3
77.5°	23.0
80°	17.4
82.5°	12.3
85°	7.1
87.5°	2.8
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)