

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P743177

Luminaire Tested: LD4D15D010-EU4DR300215IC9050-4LBSQW1B

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P743177
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D15D010-EU4DR300215IC9050-4LBSQW1B
Description: 4 INCH SQAURE DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 30° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1067.6 lumens
Efficiency: N/A
Efficacy: 67.6 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.49
Luminous Opening: Rectangular (W 0.38' x L: 0.38' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P743177
CATALOG NUMBER: LD4D15D010-EU4DR300215IC9050-4LBSQW1B

Luminous Intensity Polar Plot





TEST NUMBER: P743177

CATALOG NUMBER: LD4D15D010-EU4DR300215IC9050-4LBSQW1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96																			
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92																			
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89																			
4	103	98	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85																			
5	100	94	89	86	98	93	89	86	91	88	85	90	86	84	88	86	83	82																			
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79																			
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77																			
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74																			
9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73	72																			
10	85	78	74	71	85	78	74	71	77	73	71	76	73	71	76	73	70	69																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	262758	262758	262758
5°	255218	254918	255225
10°	221055	219493	221001
15°	144223	143455	142733
20°	71722	74410	71624
25°	36130	40742	35387
30°	14460	15759	12604
35°	6709	6429	5382
40°	2898	3217	2728
45°	2046	2533	2057
50°	703	1846	738
55°	400	761	427
60°	276	337	276
65°	181	181	181
70°	112	67	112
75°	0	59	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°

Vertical Angle: 45°

Luminance: 2533 cd/sqm



TEST NUMBER: P743177

CATALOG NUMBER: LD4D15D010-EU4DR300215IC9050-4LBSQW1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	301.9	28.3
10°-20°	486.2	45.5
20°-30°	210.1	19.7
30°-40°	47.9	4.5
40°-50°	16.4	1.5
50°-60°	4.0	0.4
60°-70°	1.0	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	998.1	93.5
0°-40°	1046.0	98.0
0°-60°	1066.4	99.9
0°-90°	1067.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1067.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3433	3433	3433	3433	3433	
5°	3322	3318	3318	3325	3322	302
15°	1820	1798	1810	1804	1801	487
25°	428	444	482	433	419	205
35°	72	73	69	68	58	49
45°	19	23	23	23	19	13
55°	3	3	6	3	3	3
65°	1	1	1	1	1	1
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	



TEST NUMBER: P743177

CATALOG NUMBER: LD4D15D010-EU4DR300215IC9050-4LBSQW1B

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3432.8	3432.8	3432.8	3432.8	3432.8
2.5°	3410.0	3407.7	3409.1	3410.7	3411.4
5°	3321.6	3318.4	3317.7	3324.6	3321.7
7.5°	3143.1	3138.5	3131.6	3147.3	3161.9
10°	2844.1	2839.0	2824.0	2831.5	2843.4
12.5°	2402.7	2386.3	2386.0	2409.6	2406.4
15°	1820.0	1798.1	1810.3	1804.4	1801.2
17.5°	1223.9	1215.5	1231.7	1226.8	1205.7
20°	880.5	882.6	913.5	898.0	879.3
22.5°	642.4	650.4	687.0	647.0	632.4
25°	427.8	443.9	482.4	432.6	419.0
27.5°	263.1	270.5	309.5	259.7	252.3
30°	163.6	160.0	178.3	153.0	142.6
32.5°	107.4	102.6	108.5	97.4	89.0
35°	71.8	73.3	68.8	68.2	57.6
37.5°	44.8	51.6	45.5	48.5	37.1
40°	29.0	37.4	32.2	35.6	27.3
42.5°	23.8	28.8	26.5	28.1	24.3
45°	18.9	23.4	23.4	23.4	19.0
47.5°	10.4	15.7	20.1	16.0	11.1
50°	5.9	7.9	15.5	8.3	6.2
52.5°	4.1	4.5	10.6	4.7	4.2
55°	3.0	3.2	5.7	3.4	3.2
57.5°	2.3	2.5	3.0	2.5	2.3
60°	1.8	1.8	2.2	2.0	1.8
62.5°	1.4	1.4	1.5	1.4	1.4
65°	1.0	1.0	1.0	1.0	1.0
67.5°	0.5	0.7	0.7	0.7	0.7
70°	0.5	0.3	0.3	0.3	0.5
72.5°	0.3	0.2	0.2	0.2	0.2
75°	0.0	0.0	0.2	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - - 90°-270°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)