

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P742670

Luminaire Tested: LD4D10D010-EU4DR650210IC9030-4LBCSSQMMS

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P742670
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D10D010-EU4DR650210IC9030-4LBCSSQMMS
Description: 4 INCH SQAURE SHALLOW CAST MATTE METALLIC SILVER TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 879.3 lumens
Efficiency: N/A
Efficacy: 75.2 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct

Input Watts (W): 11.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P742670
CATALOG NUMBER: LD4D10D010-EU4DR650210IC9030-4LBCSSQMMS

Luminous Intensity Polar Plot





TEST NUMBER: P742670

CATALOG NUMBER: LD4D10D010-EU4DR650210IC9030-4LBCSSQMMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	95	94	93																			
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85																			
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78																			
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72																			
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66																			
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61																			
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56																			
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52																			
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49																			
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	46635
5°	46515
10°	46477
15°	45046
20°	41008
25°	35739
30°	29720
35°	23550
40°	16994
45°	10737
50°	5597
55°	2973
60°	1554
65°	857
70°	359
75°	406
80°	269
85°	201

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 10737 cd/sqm



TEST NUMBER: P742670

CATALOG NUMBER: LD4D10D010-EU4DR650210IC9030-4LBCSSQMMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	75.5	8.6
10°-20°	206.8	23.5
20°-30°	252.8	28.7
30°-40°	205.1	23.3
40°-50°	102.2	11.6
50°-60°	28.5	3.2
60°-70°	6.5	0.7
70°-80°	1.7	0.2
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	535.0	60.8
0°-40°	740.1	84.2
0°-60°	870.8	99.0
0°-90°	879.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	879.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	798	
5°	793	76
15°	745	207
25°	555	253
35°	330	205
45°	130	102
55°	29	28
65°	6	6
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P742670

CATALOG NUMBER: LD4D10D010-EU4DR650210IC9030-4LBCSSQMMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	798.5
2.5°	797.9
5°	793.4
7.5°	790.8
10°	783.7
12.5°	769.1
15°	745.0
17.5°	707.2
20°	659.8
22.5°	608.6
25°	554.6
27.5°	496.7
30°	440.7
32.5°	385.4
35°	330.3
37.5°	275.2
40°	222.9
42.5°	173.9
45°	130.0
47.5°	90.6
50°	61.6
52.5°	42.5
55°	29.2
57.5°	19.7
60°	13.3
62.5°	9.3
65°	6.2
67.5°	3.2
70°	2.1
72.5°	2.0
75°	1.8
77.5°	1.1
80°	0.8
82.5°	0.6
85°	0.3
87.5°	0.2
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)