

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P742772

Luminaire Tested: LD4D10D010-EU4DR700210IC9035-4LBSQW1MW

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P742772
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D10D010-EU4DR700210IC9035-4LBSQW1MW
Description: 4 INCH SQAURE DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 876.1 lumens
Efficiency: N/A
Efficacy: 74.9 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 11.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P742772
CATALOG NUMBER: LD4D10D010-EU4DR700210IC9035-4LBSQW1MW

Luminous Intensity Polar Plot





TEST NUMBER: P742772

CATALOG NUMBER: LD4D10D010-EU4DR700210IC9035-4LBSQW1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	107622
5°	104425
10°	101505
15°	100175
20°	93542
25°	70272
30°	49683
35°	17607
40°	9257
45°	9858
50°	10199
55°	10401
60°	10467
65°	10238
70°	9680
75°	8950
80°	7928
85°	6519

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 10473 cd/sqm



TEST NUMBER: P742772

CATALOG NUMBER: LD4D10D010-EU4DR700210IC9035-4LBSQW1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	89.8	10.2
10°-20°	246.3	28.1
20°-30°	271.3	31.0
30°-40°	103.7	11.8
40°-50°	48.9	5.6
50°-60°	48.7	5.6
60°-70°	38.9	4.4
70°-80°	22.4	2.6
80°-90°	6.1	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	607.4	69.3
0°-40°	711.1	81.2
0°-60°	808.7	92.3
0°-90°	876.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	876.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	985	
5°	952	90
15°	886	246
25°	583	271
35°	132	104
45°	64	49
55°	55	49
65°	40	39
75°	21	22
85°	5	6
90°	0	



TEST NUMBER: P742772

CATALOG NUMBER: LD4D10D010-EU4DR700210IC9035-4LBSQW1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	985.0
2.5°	974.7
5°	952.1
7.5°	933.2
10°	914.9
12.5°	899.5
15°	885.6
17.5°	852.1
20°	804.5
22.5°	701.9
25°	582.9
27.5°	507.5
30°	393.8
32.5°	254.3
35°	132.0
37.5°	71.3
40°	64.9
42.5°	64.4
45°	63.8
47.5°	62.4
50°	60.0
52.5°	57.4
55°	54.6
57.5°	51.5
60°	47.9
62.5°	43.8
65°	39.6
67.5°	34.9
70°	30.3
72.5°	25.6
75°	21.2
77.5°	16.7
80°	12.6
82.5°	8.9
85°	5.2
87.5°	2.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)