

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P742785

Luminaire Tested: LD4D10D010-EU4DR700210IC9040-4LBSQW1MW

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P742785
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D10D010-EU4DR700210IC9040-4LBSQW1MW
Description: 4 INCH SQAURE DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 900.3 lumens
Efficiency: N/A
Efficacy: 76.9 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 11.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P742785

CATALOG NUMBER: LD4D10D010-EU4DR700210IC9040-4LBSQW1MW

Luminous Intensity Polar Plot





TEST NUMBER: P742785

CATALOG NUMBER: LD4D10D010-EU4DR700210IC9040-4LBSQW1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|---|--|--|--|--|--|--|----|--|--|--|--|--|--|--|--|---|
| RF | 20 | | | | | | | | | 20 | | | | | | | | | 20 | | | | | | | | | 20 | | | | | | | | | |
| RC | 80 | | | | | | | | | 50 | | | | | | | | | 30 | | | | | | | | | 10 | | | | | | | | | 0 |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 | | | | | | | | | | | | | | | | |
| RCR | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | | | | | | | | | | | | | | | | | | |
| 1 | 112 | 109 | 106 | 103 | 110 | 107 | 104 | 102 | 103 | 101 | 99 | 99 | 97 | 96 | 95 | 94 | 93 | 91 | | | | | | | | | | | | | | | | | | | |
| 2 | 106 | 100 | 95 | 91 | 103 | 98 | 94 | 90 | 95 | 91 | 88 | 92 | 89 | 86 | 89 | 87 | 85 | 83 | | | | | | | | | | | | | | | | | | | |
| 3 | 100 | 92 | 87 | 82 | 98 | 91 | 86 | 81 | 88 | 84 | 80 | 86 | 82 | 79 | 83 | 80 | 78 | 76 | | | | | | | | | | | | | | | | | | | |
| 4 | 94 | 86 | 80 | 75 | 92 | 85 | 79 | 74 | 82 | 77 | 73 | 80 | 76 | 73 | 78 | 75 | 72 | 70 | | | | | | | | | | | | | | | | | | | |
| 5 | 89 | 80 | 74 | 69 | 87 | 79 | 73 | 69 | 77 | 72 | 68 | 75 | 71 | 67 | 74 | 70 | 67 | 65 | | | | | | | | | | | | | | | | | | | |
| 6 | 85 | 75 | 68 | 64 | 83 | 74 | 68 | 64 | 73 | 67 | 63 | 71 | 66 | 63 | 70 | 66 | 62 | 61 | | | | | | | | | | | | | | | | | | | |
| 7 | 80 | 70 | 64 | 59 | 79 | 70 | 64 | 59 | 68 | 63 | 59 | 67 | 62 | 59 | 66 | 62 | 58 | 57 | | | | | | | | | | | | | | | | | | | |
| 8 | 77 | 66 | 60 | 56 | 75 | 66 | 60 | 56 | 65 | 59 | 55 | 64 | 59 | 55 | 63 | 58 | 55 | 53 | | | | | | | | | | | | | | | | | | | |
| 9 | 73 | 63 | 57 | 52 | 72 | 62 | 56 | 52 | 61 | 56 | 52 | 60 | 55 | 52 | 60 | 55 | 52 | 50 | | | | | | | | | | | | | | | | | | | |
| 10 | 70 | 59 | 53 | 49 | 69 | 59 | 53 | 49 | 58 | 53 | 49 | 57 | 52 | 49 | 57 | 52 | 49 | 48 | | | | | | | | | | | | | | | | | | | |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|--------|
| | 0° |
| 0° | 110594 |
| 5° | 107309 |
| 10° | 104323 |
| 15° | 102946 |
| 20° | 96134 |
| 25° | 72225 |
| 30° | 51058 |
| 35° | 18087 |
| 40° | 9513 |
| 45° | 10121 |
| 50° | 10488 |
| 55° | 10687 |
| 60° | 10751 |
| 65° | 10522 |
| 70° | 9935 |
| 75° | 9203 |
| 80° | 8180 |
| 85° | 6644 |

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 10757 cd/sqm



TEST NUMBER: P742785

CATALOG NUMBER: LD4D10D010-EU4DR700210IC9040-4LBSQW1MW

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 92.3 | 10.3 |
| 10°-20° | 253.1 | 28.1 |
| 20°-30° | 278.8 | 31.0 |
| 30°-40° | 106.5 | 11.8 |
| 40°-50° | 50.3 | 5.6 |
| 50°-60° | 50.0 | 5.6 |
| 60°-70° | 40.0 | 4.4 |
| 70°-80° | 23.0 | 2.6 |
| 80°-90° | 6.3 | 0.7 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 624.2 | 69.3 |
| 0°-40° | 730.7 | 81.2 |
| 0°-60° | 831.0 | 92.3 |
| 0°-90° | 900.3 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 900.3 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 1012 | |
| 5° | 978 | 92 |
| 15° | 910 | 253 |
| 25° | 599 | 279 |
| 35° | 136 | 107 |
| 45° | 66 | 50 |
| 55° | 56 | 50 |
| 65° | 41 | 40 |
| 75° | 22 | 23 |
| 85° | 5 | 6 |
| 90° | 0 | |



TEST NUMBER: P742785

CATALOG NUMBER: LD4D10D010-EU4DR700210IC9040-4LBSQW1MW

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|--------|
| 0° | 1012.2 |
| 2.5° | 1001.6 |
| 5° | 978.4 |
| 7.5° | 959.0 |
| 10° | 940.3 |
| 12.5° | 924.4 |
| 15° | 910.1 |
| 17.5° | 875.6 |
| 20° | 826.8 |
| 22.5° | 721.3 |
| 25° | 599.1 |
| 27.5° | 521.5 |
| 30° | 404.7 |
| 32.5° | 261.4 |
| 35° | 135.6 |
| 37.5° | 73.2 |
| 40° | 66.7 |
| 42.5° | 66.2 |
| 45° | 65.5 |
| 47.5° | 64.1 |
| 50° | 61.7 |
| 52.5° | 59.0 |
| 55° | 56.1 |
| 57.5° | 52.9 |
| 60° | 49.2 |
| 62.5° | 45.0 |
| 65° | 40.7 |
| 67.5° | 35.9 |
| 70° | 31.1 |
| 72.5° | 26.3 |
| 75° | 21.8 |
| 77.5° | 17.1 |
| 80° | 13.0 |
| 82.5° | 9.1 |
| 85° | 5.3 |
| 87.5° | 2.1 |
| 90° | 0.0 |

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)