

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P743718

Luminaire Tested: LD4D15D010-EU4DR700215IC9024-4LBSQW1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P743718
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D15D010-EU4DR700215IC9024-4LBSQW1B
Description: 4 INCH SQAURE DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 730.4 lumens
Efficiency: N/A
Efficacy: 46.2 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P743718
CATALOG NUMBER: LD4D15D010-EU4DR700215IC9024-4LBSQW1B

Luminous Intensity Polar Plot





TEST NUMBER: P743718

CATALOG NUMBER: LD4D15D010-EU4DR700215IC9024-4LBSQW1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	89736
5°	87062
10°	84641
15°	83524
20°	77996
25°	58590
30°	41419
35°	14672
40°	7716
45°	8220
50°	8516
55°	8667
60°	8719
65°	8532
70°	8050
75°	7472
80°	6607
85°	5391

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 8724 cd/sqm



TEST NUMBER: P743718

CATALOG NUMBER: LD4D15D010-EU4DR700215IC9024-4LBSQW1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	74.9	10.3
10°-20°	205.4	28.1
20°-30°	226.2	31.0
30°-40°	86.4	11.8
40°-50°	40.8	5.6
50°-60°	40.6	5.6
60°-70°	32.5	4.4
70°-80°	18.7	2.6
80°-90°	5.1	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	506.4	69.3
0°-40°	592.9	81.2
0°-60°	674.2	92.3
0°-90°	730.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	730.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	821	
5°	794	75
15°	738	205
25°	486	226
35°	110	86
45°	53	41
55°	46	41
65°	33	32
75°	18	19
85°	4	5
90°	0	



TEST NUMBER: P743718

CATALOG NUMBER: LD4D15D010-EU4DR700215IC9024-4LBSQW1B

CANDELA DISTRIBUTION (FULL):

0°	
0°	821.3
2.5°	812.7
5°	793.8
7.5°	778.1
10°	762.9
12.5°	750.0
15°	738.4
17.5°	710.5
20°	670.8
22.5°	585.3
25°	486.0
27.5°	423.1
30°	328.3
32.5°	212.1
35°	110.0
37.5°	59.4
40°	54.1
42.5°	53.7
45°	53.2
47.5°	52.0
50°	50.1
52.5°	47.8
55°	45.5
57.5°	42.9
60°	39.9
62.5°	36.6
65°	33.0
67.5°	29.1
70°	25.2
72.5°	21.3
75°	17.7
77.5°	13.9
80°	10.5
82.5°	7.4
85°	4.3
87.5°	1.7
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)