

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P743583

Luminaire Tested: LD4D15D010-EU4DR600215IC9027-4LBSQW1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P743583
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D15D010-EU4DR600215IC9027-4LBSQW1B
Description: 4 INCH SQAURE DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1040.7 lumens
Efficiency: N/A
Efficacy: 65.9 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P743583
CATALOG NUMBER: LD4D15D010-EU4DR600215IC9027-4LBSQW1B

Luminous Intensity Polar Plot





TEST NUMBER: P743583
 CATALOG NUMBER: LD4D15D010-EU4DR600215IC9027-4LBSQW1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93																			
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86																			
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80																			
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70																			
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66																			
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62																			
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59																			
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55																			
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	135046
5°	138370
10°	140036
15°	133408
20°	117622
25°	95131
30°	64343
35°	32252
40°	5235
45°	5115
50°	5218
55°	5296
60°	5441
65°	5558
70°	5718
75°	5783
80°	5537
85°	4638

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 75°
 Luminance: 5783 cd/sqm



TEST NUMBER: P743583

CATALOG NUMBER: LD4D15D010-EU4DR600215IC9027-4LBSQW1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	120.6	11.6
10°-20°	326.2	31.3
20°-30°	351.0	33.7
30°-40°	152.6	14.7
40°-50°	25.6	2.5
50°-60°	24.9	2.4
60°-70°	21.3	2.0
70°-80°	14.3	1.4
80°-90°	4.2	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	797.8	76.7
0°-40°	950.3	91.3
0°-60°	1000.9	96.2
0°-90°	1040.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1040.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1236	
5°	1262	121
15°	1179	326
25°	789	351
35°	242	153
45°	33	26
55°	28	25
65°	22	21
75°	14	14
85°	4	4
90°	0	



TEST NUMBER: P743583

CATALOG NUMBER: LD4D15D010-EU4DR600215IC9027-4LBSQW1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	1236.0
2.5°	1270.7
5°	1261.6
7.5°	1264.4
10°	1262.2
12.5°	1236.1
15°	1179.4
17.5°	1103.1
20°	1011.6
22.5°	913.6
25°	789.1
27.5°	631.2
30°	510.0
32.5°	393.1
35°	241.8
37.5°	103.4
40°	36.7
42.5°	33.8
45°	33.1
47.5°	32.0
50°	30.7
52.5°	29.3
55°	27.8
57.5°	26.4
60°	24.9
62.5°	23.3
65°	21.5
67.5°	19.8
70°	17.9
72.5°	15.8
75°	13.7
77.5°	11.3
80°	8.8
82.5°	6.2
85°	3.7
87.5°	1.3
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)