

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P744793

Luminaire Tested: LD4D20D010-EU4DR7020359050-4LBSQW1B

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P744793  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D20D010-EU4DR7020359050-4LBSQW1B  
Description: 4 INCH SQAURE DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 70° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1232.6 lumens  
Efficiency: N/A  
Efficacy: 53.4 lumens/watt  
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 23.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight



TEST NUMBER: P744793

CATALOG NUMBER: LD4D20D010-EU4DR7020359050-4LBSQW1B

### Luminous Intensity Polar Plot





TEST NUMBER: P744793

CATALOG NUMBER: LD4D20D010-EU4DR7020359050-4LBSQW1B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	151414
5°	146914
10°	142821
15°	140953
20°	131609
25°	98880
30°	69895
35°	24756
40°	13022
45°	13860
50°	14363
55°	14630
60°	14728
65°	14400
70°	13609
75°	12622
80°	11200
85°	9026

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 60°  
 Luminance: 14728 cd/sqm



TEST NUMBER: P744793

CATALOG NUMBER: LD4D20D010-EU4DR7020359050-4LBSQW1B

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	126.3	10.2
10°-20°	346.6	28.1
20°-30°	381.7	31.0
30°-40°	145.8	11.8
40°-50°	68.9	5.6
50°-60°	68.5	5.6
60°-70°	54.8	4.4
70°-80°	31.5	2.6
80°-90°	8.6	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	854.6	69.3
0°-40°	1000.4	81.2
0°-60°	1137.7	92.3
0°-90°	1232.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1232.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1386	
5°	1340	126
15°	1246	347
25°	820	382
35°	186	146
45°	90	69
55°	77	68
65°	56	55
75°	30	32
85°	7	9
90°	0	



TEST NUMBER: P744793

CATALOG NUMBER: LD4D20D010-EU4DR7020359050-4LBSQW1B

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1385.8
2.5°	1371.3
5°	1339.5
7.5°	1313.0
10°	1287.3
12.5°	1265.5
15°	1246.1
17.5°	1198.8
20°	1131.9
22.5°	987.5
25°	820.2
27.5°	714.0
30°	554.0
32.5°	357.9
35°	185.6
37.5°	100.3
40°	91.3
42.5°	90.6
45°	89.7
47.5°	87.8
50°	84.5
52.5°	80.7
55°	76.8
57.5°	72.4
60°	67.4
62.5°	61.6
65°	55.7
67.5°	49.2
70°	42.6
72.5°	36.0
75°	29.9
77.5°	23.5
80°	17.8
82.5°	12.5
85°	7.2
87.5°	2.9
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)