

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P743154

Luminaire Tested: LD4D15D010-EU4DR300215IC9040-4LBCSSQMMS

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P743154
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D15D010-EU4DR300215IC9040-4LBCSSQMMS
Description: 4 INCH SQAURE SHALLOW CAST MATTE METALLIC SILVER TRIM, WITH 30° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1299.1 lumens
Efficiency: N/A
Efficacy: 82.2 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.49
Luminous Opening: Rectangular (W 0.38' x L: 0.38' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P743154
CATALOG NUMBER: LD4D15D010-EU4DR300215IC9040-4LBCSSQMMS

Luminous Intensity Polar Plot





TEST NUMBER: P743154

CATALOG NUMBER: LD4D15D010-EU4DR300215IC9040-4LBCSSQMMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96																			
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92																			
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89																			
4	103	98	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85																			
5	100	94	89	86	98	93	89	86	91	88	85	90	86	84	88	86	83	82																			
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79																			
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77																			
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74																			
9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73	72																			
10	85	78	74	71	85	78	74	71	77	73	71	76	73	71	76	73	70	69																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	319745	319745	319745
5°	310570	310201	310586
10°	269003	267107	268934
15°	175509	174566	173686
20°	87272	90546	87158
25°	43960	49576	43064
30°	17606	19179	15335
35°	8167	7821	6550
40°	3527	3917	3317
45°	2490	3085	2501
50°	857	2251	905
55°	494	934	520
60°	337	413	337
65°	217	217	217
70°	134	90	134
75°	0	59	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°
 Vertical Angle: 45°
 Luminance: 3085 cd/sqm



TEST NUMBER: P743154

CATALOG NUMBER: LD4D15D010-EU4DR300215IC9040-4LBCSSQMMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	367.3	28.3
10°-20°	591.6	45.5
20°-30°	255.6	19.7
30°-40°	58.3	4.5
40°-50°	20.0	1.5
50°-60°	4.9	0.4
60°-70°	1.3	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1214.6	93.5
0°-40°	1272.8	98.0
0°-60°	1297.7	99.9
0°-90°	1299.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1299.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4177	4177	4177	4177	4177	
5°	4042	4038	4037	4046	4042	368
15°	2215	2188	2203	2196	2192	593
25°	520	540	587	526	510	249
35°	87	89	84	83	70	59
45°	23	28	28	28	23	16
55°	4	4	7	4	4	4
65°	1	1	1	1	1	1
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	



TEST NUMBER: P743154

CATALOG NUMBER: LD4D15D010-EU4DR300215IC9040-4LBCSSQMMS

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4177.3	4177.3	4177.3	4177.3	4177.3
2.5°	4149.7	4146.8	4148.4	4150.5	4151.3
5°	4042.0	4038.1	4037.2	4045.7	4042.2
7.5°	3824.8	3819.2	3810.8	3829.9	3847.8
10°	3461.0	3454.8	3436.6	3445.6	3460.1
12.5°	2923.8	2903.9	2903.5	2932.2	2928.3
15°	2214.8	2188.2	2202.9	2195.7	2191.8
17.5°	1489.4	1479.1	1498.8	1492.9	1467.2
20°	1071.4	1074.1	1111.6	1092.7	1070.0
22.5°	781.8	791.5	835.9	787.3	769.5
25°	520.5	540.2	587.0	526.5	509.9
27.5°	320.2	329.2	376.5	316.0	307.0
30°	199.2	194.6	217.0	186.2	173.5
32.5°	130.6	124.9	132.1	118.5	108.3
35°	87.4	89.2	83.7	83.1	70.1
37.5°	54.5	62.7	55.3	59.1	45.1
40°	35.3	45.5	39.2	43.3	33.2
42.5°	28.9	35.1	32.2	34.3	29.5
45°	23.0	28.5	28.5	28.5	23.1
47.5°	12.7	19.1	24.4	19.5	13.5
50°	7.2	9.6	18.9	10.0	7.6
52.5°	4.9	5.6	12.9	5.7	5.1
55°	3.7	3.9	7.0	4.1	3.9
57.5°	2.9	3.1	3.7	3.1	2.9
60°	2.2	2.2	2.7	2.5	2.2
62.5°	1.7	1.7	1.8	1.7	1.7
65°	1.2	1.2	1.2	1.2	1.2
67.5°	0.6	0.8	0.8	0.8	0.8
70°	0.6	0.4	0.4	0.4	0.6
72.5°	0.4	0.2	0.2	0.2	0.2
75°	0.0	0.0	0.2	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - - 90°-270°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)