

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P738743

Luminaire Tested: LD4D02D010-EU4DR100210IC9024-4LBCSSQMB

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P738743  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-4)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D02D010-EU4DR100210IC9024-4LBCSSQMB  
Description: 4 INCH SQAURE SHALLOW CAST MATTE BLACK TRIM, WITH 10° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 284.1 lumens  
Efficiency: N/A  
Efficacy: 55.7 lumens/watt  
Spacing Criteria (0/90/45): 0.17 / 0.17 / 0.18  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 5.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight



TEST NUMBER: P738743

CATALOG NUMBER: LD4D02D010-EU4DR100210IC9024-4LBCSSQMB

### Luminous Intensity Polar Plot





TEST NUMBER: P738743

CATALOG NUMBER: LD4D02D010-EU4DR100210IC9024-4LBCSSQMB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									20
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0										
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100									100										
1	116	114	113	111	114	112	111	109	108	107	106	104	104	103	101	101	100	98									98										
2	113	110	108	106	111	108	106	104	105	104	102	103	101	100	99	98	97	96									97										
3	111	107	104	102	109	106	103	101	103	101	99	101	99	98	97	96	95	94									95										
4	108	104	101	99	107	103	100	98	101	99	97	99	97	96	96	95	94	93									94										
5	106	102	99	96	105	101	98	96	99	97	95	98	96	94	94	93	92	91									93										
6	104	100	96	94	103	99	96	94	98	95	93	97	94	93	93	92	91	90									91										
7	103	98	95	93	102	97	94	92	96	94	92	95	93	92	92	91	90	89									90										
8	101	96	93	91	100	96	93	91	95	92	91	94	92	90	90	89	88	87									89										
9	100	95	92	90	99	94	92	90	94	91	90	93	91	89	89	88	87	86									88										
10	98	94	91	89	98	93	91	89	93	90	89	92	90	88	88	87	86	85									87										

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	676018
5°	320567
10°	65747
15°	18053
20°	7279
25°	3894
30°	2309
35°	1494
40°	998
45°	649
50°	357
55°	267
60°	153
65°	0
70°	0
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 649 cd/sqm



TEST NUMBER: P738743

CATALOG NUMBER: LD4D02D010-EU4DR100210IC9024-4LBCSSQMB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	202.1	71.1
10°-20°	54.7	19.2
20°-30°	15.7	5.5
30°-40°	7.1	2.5
40°-50°	3.3	1.1
50°-60°	1.1	0.4
60°-70°	0.3	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	272.4	95.9
0°-40°	279.5	98.4
0°-60°	283.9	99.9
0°-90°	284.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	284.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	6187	
5°	2923	202
15°	160	55
25°	32	16
35°	11	7
45°	4	3
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P738743

CATALOG NUMBER: LD4D02D010-EU4DR100210IC9024-4LBCSSQMB

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	6187.2
0.5°	6133.7
1°	5996.7
1.5°	5732.4
2°	5436.4
2.5°	5045.6
3°	4611.2
3.5°	4190.8
4°	3737.5
4.5°	3319.9
5°	2922.8
5.5°	2562.9
6°	2219.8
6.5°	1918.3
7°	1634.3
7.5°	1391.8
8°	1176.7
8.5°	988.3
9°	825.2
9.5°	700.8
10°	592.6
12.5°	282.6
15°	159.6
17.5°	97.0
20°	62.6
22.5°	43.6
25°	32.3
27.5°	23.9
30°	18.3
32.5°	14.1
35°	11.2
37.5°	8.4
40°	7.0
42.5°	5.6
45°	4.2
47.5°	2.8
50°	2.1
52.5°	1.4
55°	1.4
57.5°	0.7
60°	0.7
62.5°	0.7
65°	0.0



TEST NUMBER: P738743

CATALOG NUMBER: LD4D02D010-EU4DR100210IC9024-4LBCSSQMB

**CANDELA DISTRIBUTION (continued):**

	0°
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



67.5°		0.0
70°		0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)