

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P739057

Luminaire Tested: LD4D02D010-EU4DR300210IC9024-4LBCSSQMW

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P739057
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D02D010-EU4DR300210IC9024-4LBCSSQMW
Description: 4 INCH SQAURE SHALLOW CAST MATTE WHITE TRIM, WITH 30° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 271.2 lumens
Efficiency: N/A
Efficacy: 53.2 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.49
Luminous Opening: Rectangular (W 0.38' x L: 0.38' x H: 0')
CIE Type: Direct

Input Watts (W): 5.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P739057

CATALOG NUMBER: LD4D02D010-EU4DR300210IC9024-4LBCSSQMW

Luminous Intensity Polar Plot





TEST NUMBER: P739057

CATALOG NUMBER: LD4D02D010-EU4DR300210IC9024-4LBCSSQMW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96																			
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92																			
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89																			
4	103	98	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85																			
5	100	94	89	86	98	93	89	86	91	88	85	90	86	84	88	86	83	82																			
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79																			
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77																			
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74																			
9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73	72																			
10	85	78	74	71	85	78	74	71	77	73	71	76	73	71	76	73	70	69																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	66746	66746	66746
5°	64826	64757	64834
10°	56148	55752	56140
15°	36634	36444	36254
20°	18214	18898	18189
25°	9172	10354	8995
30°	3677	4004	3200
35°	1701	1635	1374
40°	739	819	689
45°	520	649	520
50°	179	476	191
55°	93	187	107
60°	77	92	77
65°	36	36	36
70°	22	22	22
75°	0	30	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°

Vertical Angle: 45°

Luminance: 649 cd/sqm



TEST NUMBER: P739057

CATALOG NUMBER: LD4D02D010-EU4DR300210IC9024-4LBCSSQMW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	76.7	28.3
10°-20°	123.5	45.5
20°-30°	53.4	19.7
30°-40°	12.2	4.5
40°-50°	4.2	1.5
50°-60°	1.0	0.4
60°-70°	0.3	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	253.5	93.5
0°-40°	265.7	98.0
0°-60°	270.9	99.9
0°-90°	271.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	271.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	872	872	872	872	872	
5°	844	843	843	844	844	77
15°	462	457	460	458	458	124
25°	109	113	123	110	106	52
35°	18	19	18	17	15	12
45°	5	6	6	6	5	3
55°	1	1	1	1	1	1
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P739057

CATALOG NUMBER: LD4D02D010-EU4DR300210IC9024-4LBCSSQMW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	872.0	872.0	872.0	872.0	872.0
2.5°	866.2	865.6	866.0	866.4	866.5
5°	843.7	842.9	842.8	844.5	843.8
7.5°	798.4	797.3	795.5	799.4	803.2
10°	722.4	721.2	717.3	719.2	722.3
12.5°	610.3	606.2	606.1	612.1	611.3
15°	462.3	456.8	459.9	458.4	457.5
17.5°	310.9	308.8	312.9	311.6	306.3
20°	223.6	224.2	232.0	228.1	223.3
22.5°	163.2	165.2	174.5	164.4	160.7
25°	108.6	112.8	122.6	109.9	106.5
27.5°	66.8	68.7	78.6	65.9	64.1
30°	41.6	40.6	45.3	38.8	36.2
32.5°	27.3	26.1	27.6	24.8	22.6
35°	18.2	18.6	17.5	17.4	14.7
37.5°	11.4	13.1	11.6	12.3	9.4
40°	7.4	9.5	8.2	9.1	6.9
42.5°	6.0	7.3	6.7	7.2	6.2
45°	4.8	6.0	6.0	6.0	4.8
47.5°	2.6	4.0	5.1	4.1	2.8
50°	1.5	2.0	4.0	2.1	1.6
52.5°	1.0	1.1	2.7	1.2	1.1
55°	0.7	0.8	1.4	0.9	0.8
57.5°	0.6	0.6	0.7	0.6	0.6
60°	0.5	0.5	0.6	0.5	0.5
62.5°	0.3	0.3	0.4	0.3	0.3
65°	0.2	0.2	0.2	0.2	0.2
67.5°	0.1	0.2	0.2	0.2	0.2
70°	0.1	0.1	0.1	0.1	0.1
72.5°	0.1	0.1	0.1	0.1	0.1
75°	0.0	0.0	0.1	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - - 90°-270°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)