

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P743631

Luminaire Tested: LD4D15D010-EU4DR600215IC9050-4LBSQW1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P743631
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D15D010-EU4DR600215IC9050-4LBSQW1B
Description: 4 INCH SQAURE DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1152.0 lumens
Efficiency: N/A
Efficacy: 72.9 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P743631
CATALOG NUMBER: LD4D15D010-EU4DR600215IC9050-4LBSQW1B

Luminous Intensity Polar Plot





TEST NUMBER: P743631

CATALOG NUMBER: LD4D15D010-EU4DR600215IC9050-4LBSQW1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93			93																
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86			86																
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80			80																
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75			75																
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70			70																
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66			66																
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62			62																
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59			59																
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55			55																
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53			53																

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	149491
5°	153165
10°	155025
15°	147672
20°	130202
25°	105318
30°	71232
35°	35693
40°	5791
45°	5671
50°	5779
55°	5867
60°	6031
65°	6153
70°	6325
75°	6374
80°	6166
85°	5140

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 75°
 Luminance: 6374 cd/sqm



TEST NUMBER: P743631

CATALOG NUMBER: LD4D15D010-EU4DR600215IC9050-4LBSQW1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	133.5	11.6
10°-20°	361.1	31.3
20°-30°	388.5	33.7
30°-40°	168.9	14.7
40°-50°	28.4	2.5
50°-60°	27.6	2.4
60°-70°	23.6	2.0
70°-80°	15.8	1.4
80°-90°	4.7	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	883.1	76.7
0°-40°	1052.0	91.3
0°-60°	1108.0	96.2
0°-90°	1152.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1152.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1368	
5°	1396	133
15°	1306	361
25°	874	389
35°	268	169
45°	37	28
55°	31	28
65°	24	24
75°	15	16
85°	4	5
90°	0	



TEST NUMBER: P743631

CATALOG NUMBER: LD4D15D010-EU4DR600215IC9050-4LBSQW1B

CANDELA DISTRIBUTION (FULL):

0°	
0°	1368.2
2.5°	1406.7
5°	1396.5
7.5°	1399.7
10°	1397.3
12.5°	1368.4
15°	1305.5
17.5°	1221.1
20°	1119.8
22.5°	1011.4
25°	873.6
27.5°	698.7
30°	564.6
32.5°	435.2
35°	267.6
37.5°	114.5
40°	40.6
42.5°	37.4
45°	36.7
47.5°	35.4
50°	34.0
52.5°	32.4
55°	30.8
57.5°	29.2
60°	27.6
62.5°	25.8
65°	23.8
67.5°	21.9
70°	19.8
72.5°	17.5
75°	15.1
77.5°	12.5
80°	9.8
82.5°	6.9
85°	4.1
87.5°	1.4
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)