

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P743779

Luminaire Tested: LD4D15D010-EU4DR700215IC9050-4LBSQW1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P743779
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D15D010-EU4DR700215IC9050-4LBSQW1B
Description: 4 INCH SQAURE DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 897.6 lumens
Efficiency: N/A
Efficacy: 56.8 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P743779

CATALOG NUMBER: LD4D15D010-EU4DR700215IC9050-4LBSQW1B

Luminous Intensity Polar Plot





TEST NUMBER: P743779

CATALOG NUMBER: LD4D15D010-EU4DR700215IC9050-4LBSQW1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	110266
5°	106991
10°	104012
15°	102641
20°	95844
25°	72008
30°	50907
35°	18033
40°	9485
45°	10105
50°	10454
55°	10648
60°	10708
65°	10496
70°	9903
75°	9161
80°	8117
85°	6644

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 10717 cd/sqm



TEST NUMBER: P743779

CATALOG NUMBER: LD4D15D010-EU4DR700215IC9050-4LBSQW1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	92.0	10.3
10°-20°	252.4	28.1
20°-30°	278.0	31.0
30°-40°	106.2	11.8
40°-50°	50.2	5.6
50°-60°	49.8	5.6
60°-70°	39.9	4.4
70°-80°	22.9	2.6
80°-90°	6.2	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	622.4	69.3
0°-40°	728.6	81.2
0°-60°	828.5	92.3
0°-90°	897.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	897.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1009	
5°	976	92
15°	907	252
25°	597	278
35°	135	106
45°	65	50
55°	56	50
65°	41	40
75°	22	23
85°	5	6
90°	0	



TEST NUMBER: P743779

CATALOG NUMBER: LD4D15D010-EU4DR700215IC9050-4LBSQW1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	1009.2
2.5°	998.7
5°	975.5
7.5°	956.1
10°	937.5
12.5°	921.6
15°	907.4
17.5°	873.1
20°	824.3
22.5°	719.2
25°	597.3
27.5°	520.0
30°	403.5
32.5°	260.6
35°	135.2
37.5°	73.0
40°	66.5
42.5°	66.0
45°	65.4
47.5°	63.9
50°	61.5
52.5°	58.8
55°	55.9
57.5°	52.7
60°	49.0
62.5°	44.9
65°	40.6
67.5°	35.8
70°	31.0
72.5°	26.2
75°	21.7
77.5°	17.1
80°	12.9
82.5°	9.1
85°	5.3
87.5°	2.1
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)