

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P744742

Luminaire Tested: LD4D20D010-EU4DR7020359027-4LBSQW1MW

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P744742  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D20D010-EU4DR7020359027-4LBSQW1MW  
Description: 4 INCH SQAURE DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 70° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1482.9 lumens  
Efficiency: N/A  
Efficacy: 64.2 lumens/watt  
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 23.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight



TEST NUMBER: P744742  
CATALOG NUMBER: LD4D20D010-EU4DR7020359027-4LBSQW1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P744742

CATALOG NUMBER: LD4D20D010-EU4DR7020359027-4LBSQW1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	182170
5°	176757
10°	171823
15°	169571
20°	158340
25°	118953
30°	84101
35°	29784
40°	15661
45°	16672
50°	17270
55°	17601
60°	17700
65°	17322
70°	16356
75°	15155
80°	13465
85°	10907

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 57.5°  
 Luminance: 17712 cd/sqm



TEST NUMBER: P744742

CATALOG NUMBER: LD4D20D010-EU4DR7020359027-4LBSQW1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	152.0	10.3
10°-20°	416.9	28.1
20°-30°	459.2	31.0
30°-40°	175.5	11.8
40°-50°	82.8	5.6
50°-60°	82.3	5.6
60°-70°	65.9	4.4
70°-80°	37.9	2.6
80°-90°	10.3	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1028.2	69.3
0°-40°	1203.6	81.2
0°-60°	1368.8	92.3
0°-90°	1482.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1482.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1667	
5°	1612	152
15°	1499	417
25°	987	459
35°	223	175
45°	108	83
55°	92	82
65°	67	66
75°	36	38
85°	9	10
90°	0	



TEST NUMBER: P744742

CATALOG NUMBER: LD4D20D010-EU4DR7020359027-4LBSQW1MW

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1667.3
2.5°	1649.9
5°	1611.6
7.5°	1579.6
10°	1548.7
12.5°	1522.6
15°	1499.1
17.5°	1442.3
20°	1361.8
22.5°	1188.2
25°	986.7
27.5°	859.0
30°	666.6
32.5°	430.6
35°	223.3
37.5°	120.7
40°	109.8
42.5°	109.0
45°	107.9
47.5°	105.6
50°	101.6
52.5°	97.1
55°	92.4
57.5°	87.1
60°	81.0
62.5°	74.2
65°	67.0
67.5°	59.1
70°	51.2
72.5°	43.3
75°	35.9
77.5°	28.2
80°	21.4
82.5°	15.1
85°	8.7
87.5°	3.4
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)