

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P744119

Luminaire Tested: LD4D20D010-EU4DR3020359030-4LBCSSQMB

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P744119
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D20D010-EU4DR3020359030-4LBCSSQMB
Description: 4 INCH SQAURE SHALLOW CAST MATTE BLACK TRIM, WITH 30° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1644.3 lumens
Efficiency: N/A
Efficacy: 71.2 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.49
Luminous Opening: Rectangular (W 0.38' x L: 0.38' x H: 0')
CIE Type: Direct

Input Watts (W): 23.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P744119
CATALOG NUMBER: LD4D20D010-EU4DR3020359030-4LBCSSQMB

Luminous Intensity Polar Plot





TEST NUMBER: P744119

CATALOG NUMBER: LD4D20D010-EU4DR3020359030-4LBCSSQMB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						100													
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96						96													
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92						92													
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89						89													
4	103	98	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85						85													
5	100	94	89	86	98	93	89	86	91	88	85	90	86	84	88	86	83	82						82													
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79						79													
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77						77													
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74						74													
9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73	72						72													
10	85	78	74	71	85	78	74	71	77	73	71	76	73	71	76	73	70	69						69													

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	404716	404716	404716
5°	393100	392639	393115
10°	340486	338085	340401
15°	222143	220955	219845
20°	110462	114608	110316
25°	55640	62743	54508
30°	22273	24279	19409
35°	10335	9896	8298
40°	4456	4956	4207
45°	3139	3908	3172
50°	1084	2846	1143
55°	627	1174	654
60°	444	520	444
65°	272	272	272
70°	179	112	179
75°	0	89	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°
 Vertical Angle: 45°
 Luminance: 3908 cd/sqm



TEST NUMBER: P744119

CATALOG NUMBER: LD4D20D010-EU4DR3020359030-4LBCSSQMB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	464.9	28.3
10°-20°	748.8	45.5
20°-30°	323.6	19.7
30°-40°	73.8	4.5
40°-50°	25.3	1.5
50°-60°	6.2	0.4
60°-70°	1.6	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1537.3	93.5
0°-40°	1611.1	98.0
0°-60°	1642.6	99.9
0°-90°	1644.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1644.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	5287	5287	5287	5287	5287	
5°	5116	5111	5110	5121	5116	465
15°	2803	2770	2788	2779	2774	751
25°	659	684	743	666	645	315
35°	111	113	106	105	89	75
45°	29	36	36	36	29	21
55°	5	5	9	5	5	5
65°	2	2	2	2	2	2
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	



TEST NUMBER: P744119

CATALOG NUMBER: LD4D20D010-EU4DR3020359030-4LBCSSQMB

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	5287.4	5287.4	5287.4	5287.4	5287.4
2.5°	5252.4	5248.7	5250.8	5253.4	5254.4
5°	5116.1	5111.1	5110.1	5120.7	5116.3
7.5°	4841.1	4834.2	4823.5	4847.7	4870.3
10°	4380.7	4372.9	4349.8	4361.2	4379.6
12.5°	3700.7	3675.6	3675.1	3711.4	3706.5
15°	2803.3	2769.6	2788.3	2779.2	2774.3
17.5°	1885.2	1872.2	1897.1	1889.6	1857.2
20°	1356.1	1359.5	1407.0	1383.1	1354.3
22.5°	989.6	1001.7	1058.1	996.6	974.0
25°	658.8	683.8	742.9	666.4	645.4
27.5°	405.2	416.6	476.6	400.0	388.6
30°	252.0	246.4	274.7	235.7	219.6
32.5°	165.4	158.1	167.2	150.1	137.0
35°	110.6	112.9	105.9	105.1	88.8
37.5°	69.0	79.4	70.1	74.8	57.1
40°	44.6	57.6	49.6	54.8	42.1
42.5°	36.6	44.4	40.7	43.4	37.4
45°	29.0	36.1	36.1	36.1	29.3
47.5°	16.1	24.1	30.9	24.6	17.1
50°	9.1	12.2	23.9	12.7	9.6
52.5°	6.2	7.0	16.3	7.3	6.5
55°	4.7	4.9	8.8	5.2	4.9
57.5°	3.6	3.9	4.7	3.9	3.6
60°	2.9	2.9	3.4	3.1	2.9
62.5°	2.1	2.1	2.3	2.1	2.1
65°	1.5	1.5	1.5	1.5	1.5
67.5°	0.8	1.0	1.0	1.0	1.0
70°	0.8	0.5	0.5	0.5	0.8
72.5°	0.5	0.3	0.3	0.3	0.3
75°	0.0	0.0	0.3	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - - 90°-270°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)