

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P745352

Luminaire Tested: LD4D25D010-EU4DR5020359024-4LBSQW1B

Issue Date: 1/30/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P745352  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-44)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 1/30/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D25D010-EU4DR5020359024-4LBSQW1B  
Description: 4 INCH SQAURE DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 50° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1881.5 lumens  
Efficiency: N/A  
Efficacy: 75.0 lumens/watt  
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.73  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 25.1  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight



TEST NUMBER: P745352

CATALOG NUMBER: LD4D25D010-EU4DR5020359024-4LBSQW1B

### Luminous Intensity Polar Plot





TEST NUMBER: P745352

CATALOG NUMBER: LD4D25D010-EU4DR5020359024-4LBSQW1B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100															
1	114	112	109	107	112	110	108	106	106	104	102	102	101	99	98	97	97	95				95															
2	109	105	101	98	107	103	100	97	100	98	95	97	95	93	95	93	91	90				90															
3	105	99	95	91	103	98	94	90	95	92	89	93	90	88	91	88	86	85				85															
4	100	94	89	85	99	93	88	85	90	87	84	89	85	83	87	84	82	80				80															
5	96	89	84	80	95	88	83	79	86	82	79	85	81	78	83	80	77	76				76															
6	92	84	79	75	91	83	79	75	82	78	74	81	77	74	79	76	74	72				72															
7	88	80	75	71	87	79	74	71	78	74	71	77	73	70	76	73	70	69				69															
8	85	76	71	67	84	76	71	67	75	70	67	74	70	67	73	69	66	65				65															
9	81	73	68	64	80	72	67	64	71	67	64	71	67	64	70	66	63	62				62															
10	78	70	64	61	77	69	64	61	68	64	61	68	64	61	67	63	60	59				59															

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	331235
5°	327762
10°	322366
15°	293545
20°	244254
25°	173384
30°	91771
35°	37401
40°	13892
45°	6351
50°	2618
55°	1372
60°	677
65°	181
70°	0
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 6351 cd/sqm



TEST NUMBER: P745352

CATALOG NUMBER: LD4D25D010-EU4DR5020359024-4LBSQW1B

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	282.5	15.0
10°-20°	713.9	37.9
20°-30°	641.2	34.1
30°-40°	200.8	10.7
40°-50°	35.1	1.9
50°-60°	7.0	0.4
60°-70°	1.0	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1637.5	87.0
0°-40°	1838.3	97.7
0°-60°	1880.5	99.9
0°-90°	1881.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1881.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3032	
5°	2988	282
15°	2595	714
25°	1438	641
35°	280	201
45°	41	35
55°	7	7
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P745352

CATALOG NUMBER: LD4D25D010-EU4DR5020359024-4LBSQW1B

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	3031.6
2.5°	3016.5
5°	2988.4
7.5°	2945.5
10°	2905.6
12.5°	2777.8
15°	2595.1
17.5°	2363.0
20°	2100.7
22.5°	1797.3
25°	1438.2
27.5°	1057.4
30°	727.4
32.5°	473.6
35°	280.4
37.5°	161.0
40°	97.4
42.5°	63.4
45°	41.1
47.5°	25.0
50°	15.4
52.5°	10.5
55°	7.2
57.5°	4.9
60°	3.1
62.5°	1.8
65°	0.7
67.5°	0.2
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)