

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P743832

Luminaire Tested: LD4D20D010-EU4DR1015209035-4LBSQW1MW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P743832
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-4)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D20D010-EU4DR1015209035-4LBSQW1MW
Description: 4 INCH SQAURE DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 10° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1750.7 lumens
Efficiency: N/A
Efficacy: 75.8 lumens/watt
Spacing Criteria (0/90/45): 0.17 / 0.17 / 0.18
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 23.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P743832

CATALOG NUMBER: LD4D20D010-EU4DR1015209035-4LBSQW1MW

Luminous Intensity Polar Plot





TEST NUMBER: P743832

CATALOG NUMBER: LD4D20D010-EU4DR1015209035-4LBSQW1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	116	114	113	111	114	112	111	109	108	107	106		104	104	103		101	101	100	98
2	113	110	108	106	111	108	106	104	105	104	102		103	101	100		100	99	98	97
3	111	107	104	102	109	106	103	101	103	101	99		101	99	98		99	98	96	95
4	108	104	101	99	107	103	100	98	101	99	97		99	97	96		98	96	95	94
5	106	102	99	96	105	101	98	96	99	97	95		98	96	94		97	95	94	93
6	104	100	96	94	103	99	96	94	98	95	93		97	94	93		96	94	92	91
7	103	98	95	93	102	97	94	92	96	94	92		95	93	92		95	93	91	90
8	101	96	93	91	100	96	93	91	95	92	91		94	92	90		93	92	90	89
9	100	95	92	90	99	94	92	90	94	91	90		93	91	89		93	91	89	88
10	98	94	91	89	98	93	91	89	93	90	88		92	90	88		92	90	88	87

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	4164998
5°	1975029
10°	405054
15°	111203
20°	44812
25°	24015
30°	14206
35°	9243
40°	6176
45°	4017
50°	2210
55°	1657
60°	940
65°	0
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 4017 cd/sqm



TEST NUMBER: P743832

CATALOG NUMBER: LD4D20D010-EU4DR1015209035-4LBSQW1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1244.9	71.1
10°-20°	336.9	19.2
20°-30°	96.4	5.5
30°-40°	44.0	2.5
40°-50°	20.2	1.2
50°-60°	6.7	0.4
60°-70°	1.6	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1678.2	95.9
0°-40°	1722.2	98.4
0°-60°	1749.2	99.9
0°-90°	1750.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1750.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	38120	
5°	18008	###
15°	983	337
25°	199	96
35°	69	44
45°	26	20
55°	9	7
65°	0	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P743832

CATALOG NUMBER: LD4D20D010-EU4DR1015209035-4LBSQW1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	38119.8
0.5°	37790.7
1°	36946.2
1.5°	35317.8
2°	33494.5
2.5°	31086.6
3°	28410.1
3.5°	25820.3
4°	23026.9
4.5°	20454.4
5°	18007.5
5.5°	15790.1
6°	13676.7
6.5°	11818.8
7°	10069.1
7.5°	8575.0
8°	7249.8
8.5°	6089.1
9°	5084.4
9.5°	4317.8
10°	3650.9
12.5°	1741.0
15°	983.1
17.5°	597.7
20°	385.4
22.5°	268.5
25°	199.2
27.5°	147.2
30°	112.6
32.5°	86.6
35°	69.3
37.5°	52.0
40°	43.3
42.5°	34.6
45°	26.0
47.5°	17.3
50°	13.0
52.5°	8.7
55°	8.7
57.5°	4.3
60°	4.3
62.5°	4.3
65°	0.0



TEST NUMBER: P743832

CATALOG NUMBER: LD4D20D010-EU4DR1015209035-4LBSQW1MW

CANDELA DISTRIBUTION (continued):

	0°
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





67.5°		0.0
70°		0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)