

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P745522

Luminaire Tested: LD4D25D010-EU4DR6020359027-4LBSQW1MW

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P745522
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D25D010-EU4DR6020359027-4LBSQW1MW
Description: 4 INCH SQAURE DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2080.1 lumens
Efficiency: N/A
Efficacy: 82.9 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 25.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P745522

CATALOG NUMBER: LD4D25D010-EU4DR6020359027-4LBSQW1MW

Luminous Intensity Polar Plot





TEST NUMBER: P745522

CATALOG NUMBER: LD4D25D010-EU4DR6020359027-4LBSQW1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93			93																
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86			86																
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80			80																
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75			75																
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70			70																
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66			66																
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62			62																
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59			59																
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55			55																
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53			53																

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	269929
5°	276575
10°	279906
15°	266646
20°	235104
25°	190153
30°	128624
35°	64451
40°	10455
45°	10229
50°	10437
55°	10591
60°	10882
65°	11143
70°	11405
75°	11525
80°	11137
85°	9277

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 75°
 Luminance: 11525 cd/sqm



TEST NUMBER: P745522

CATALOG NUMBER: LD4D25D010-EU4DR6020359027-4LBSQW1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	241.0	11.6
10°-20°	652.1	31.3
20°-30°	701.5	33.7
30°-40°	304.9	14.7
40°-50°	51.2	2.5
50°-60°	49.8	2.4
60°-70°	42.6	2.0
70°-80°	28.5	1.4
80°-90°	8.5	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1594.6	76.7
0°-40°	1899.5	91.3
0°-60°	2000.5	96.2
0°-90°	2080.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2080.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2470	
5°	2522	241
15°	2357	652
25°	1577	702
35°	483	305
45°	66	51
55°	56	50
65°	43	43
75°	27	28
85°	7	9
90°	0	



TEST NUMBER: P745522

CATALOG NUMBER: LD4D25D010-EU4DR6020359027-4LBSQW1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	2470.5
2.5°	2540.0
5°	2521.7
7.5°	2527.5
10°	2522.9
12.5°	2470.9
15°	2357.3
17.5°	2204.9
20°	2022.0
22.5°	1826.2
25°	1577.3
27.5°	1261.6
30°	1019.5
32.5°	785.8
35°	483.2
37.5°	206.7
40°	73.3
42.5°	67.5
45°	66.2
47.5°	64.0
50°	61.4
52.5°	58.5
55°	55.6
57.5°	52.7
60°	49.8
62.5°	46.6
65°	43.1
67.5°	39.5
70°	35.7
72.5°	31.5
75°	27.3
77.5°	22.5
80°	17.7
82.5°	12.5
85°	7.4
87.5°	2.6
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)