

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P745589

Luminaire Tested: LD4D25D010-EU4DR6520359027-4LBCSSQMMS

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P745589
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D25D010-EU4DR6520359027-4LBCSSQMMS
Description: 4 INCH SQAURE SHALLOW CAST MATTE METALLIC SILVER TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2030.7 lumens
Efficiency: N/A
Efficacy: 80.9 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct

Input Watts (W): 25.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P745589
CATALOG NUMBER: LD4D25D010-EU4DR6520359027-4LBCSSQMMS

Luminous Intensity Polar Plot





TEST NUMBER: P745589

CATALOG NUMBER: LD4D25D010-EU4DR6520359027-4LBCSSQMMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93																			
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85																			
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78																			
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72																			
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66																			
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61																			
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56																			
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52																			
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49																			
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	107685
5°	107410
10°	107324
15°	104010
20°	94689
25°	82517
30°	68633
35°	54379
40°	39249
45°	24795
50°	12929
55°	6873
60°	3609
65°	1990
70°	837
75°	925
80°	639
85°	536

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 24795 cd/sqm



TEST NUMBER: P745589

CATALOG NUMBER: LD4D25D010-EU4DR6520359027-4LBCSSQMMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	174.4	8.6
10°-20°	477.5	23.5
20°-30°	583.6	28.7
30°-40°	473.5	23.3
40°-50°	236.0	11.6
50°-60°	65.8	3.2
60°-70°	15.0	0.7
70°-80°	3.9	0.2
80°-90°	1.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1235.5	60.8
0°-40°	1709.0	84.2
0°-60°	2010.8	99.0
0°-90°	2030.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2030.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1844	
5°	1832	174
15°	1720	477
25°	1280	584
35°	763	474
45°	300	236
55°	68	66
65°	14	15
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P745589

CATALOG NUMBER: LD4D25D010-EU4DR6520359027-4LBCSSQMMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	1843.8
2.5°	1842.4
5°	1832.1
7.5°	1826.2
10°	1809.7
12.5°	1776.0
15°	1720.2
17.5°	1633.0
20°	1523.5
22.5°	1405.4
25°	1280.5
27.5°	1146.9
30°	1017.7
32.5°	890.1
35°	762.7
37.5°	635.6
40°	514.8
42.5°	401.5
45°	300.2
47.5°	209.2
50°	142.3
52.5°	98.1
55°	67.5
57.5°	45.5
60°	30.9
62.5°	21.4
65°	14.4
67.5°	7.3
70°	4.9
72.5°	4.6
75°	4.1
77.5°	2.7
80°	1.9
82.5°	1.4
85°	0.8
87.5°	0.5
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)