

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P745534

Luminaire Tested: LD4D25D010-EU4DR6020359030-4LBSQW1B

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P745534  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D25D010-EU4DR6020359030-4LBSQW1B  
Description: 4 INCH SQAURE DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 60° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1906.8 lumens  
Efficiency: N/A  
Efficacy: 76.0 lumens/watt  
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 25.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight



TEST NUMBER: P745534

CATALOG NUMBER: LD4D25D010-EU4DR6020359030-4LBSQW1B

### Luminous Intensity Polar Plot





TEST NUMBER: P745534

CATALOG NUMBER: LD4D25D010-EU4DR6020359030-4LBSQW1B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93																			
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86																			
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80																			
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70																			
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66																			
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62																			
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59																			
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55																			
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	247432
5°	253521
10°	256574
15°	244419
20°	215500
25°	174300
30°	117900
35°	59075
40°	9585
45°	9379
50°	9570
55°	9715
60°	9986
65°	10212
70°	10446
75°	10554
80°	10193
85°	8525

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 75°  
 Luminance: 10554 cd/sqm



TEST NUMBER: P745534

CATALOG NUMBER: LD4D25D010-EU4DR6020359030-4LBSQW1B

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	220.9	11.6
10°-20°	597.7	31.3
20°-30°	643.1	33.7
30°-40°	279.5	14.7
40°-50°	47.0	2.5
50°-60°	45.7	2.4
60°-70°	39.1	2.0
70°-80°	26.1	1.4
80°-90°	7.8	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1461.7	76.7
0°-40°	1741.2	91.3
0°-60°	1833.8	96.2
0°-90°	1906.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1906.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2265	
5°	2312	221
15°	2161	598
25°	1446	643
35°	443	280
45°	61	47
55°	51	46
65°	40	39
75°	25	26
85°	7	8
90°	0	



TEST NUMBER: P745534

CATALOG NUMBER: LD4D25D010-EU4DR6020359030-4LBSQW1B

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2264.6
2.5°	2328.2
5°	2311.5
7.5°	2316.7
10°	2312.6
12.5°	2264.9
15°	2160.8
17.5°	2021.1
20°	1853.4
22.5°	1674.0
25°	1445.8
27.5°	1156.4
30°	934.5
32.5°	720.3
35°	442.9
37.5°	189.5
40°	67.2
42.5°	61.9
45°	60.7
47.5°	58.7
50°	56.3
52.5°	53.6
55°	51.0
57.5°	48.4
60°	45.7
62.5°	42.7
65°	39.5
67.5°	36.3
70°	32.7
72.5°	28.9
75°	25.0
77.5°	20.6
80°	16.2
82.5°	11.5
85°	6.8
87.5°	2.3
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)