

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P744001

Luminaire Tested: LD4D20D010-EU4DR2015309040-4LBSQW1MW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P744001
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-36)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D20D010-EU4DR2015309040-4LBSQW1MW
Description: 4 INCH SQAURE DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 20° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1832.0 lumens
Efficiency: N/A
Efficacy: 79.3 lumens/watt
Spacing Criteria (0/90/45): 0.34 / 0.34 / 0.36
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 23.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P744001
CATALOG NUMBER: LD4D20D010-EU4DR2015309040-4LBSQW1MW

Luminous Intensity Polar Plot





TEST NUMBER: P744001

CATALOG NUMBER: LD4D20D010-EU4DR2015309040-4LBSQW1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						100													
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	100	99	98	98	96	95	94													
2	111	108	105	102	109	106	104	101	103	101	99	100	99	97	98	96	95	98	96	95	98	96	95	94													
3	108	103	100	97	106	102	99	96	100	97	95	97	95	93	95	93	92	98	96	95	98	96	95	94													
4	105	99	96	93	103	98	95	92	96	93	91	95	92	90	93	91	89	93	91	89	93	91	89	88													
5	102	96	92	89	100	95	91	89	94	90	88	92	89	87	91	88	86	91	88	86	91	88	86	85													
6	99	93	89	86	98	92	88	86	91	87	85	90	87	84	88	86	84	88	86	84	88	86	84	83													
7	96	90	86	83	95	89	86	83	88	85	82	87	84	82	86	84	82	86	84	82	86	84	82	81													
8	94	87	83	81	93	87	83	80	86	83	80	85	82	80	84	82	80	84	82	80	84	82	80	79													
9	91	85	81	78	91	85	81	78	84	80	78	83	80	78	82	80	78	82	80	78	82	80	78	77													
10	89	83	79	76	88	82	79	76	82	78	76	81	78	76	81	78	76	81	78	76	81	78	76	75													

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1139273
5°	1027837
10°	576876
15°	293239
20°	124156
25°	57312
30°	30342
35°	16353
40°	8743
45°	5161
50°	2992
55°	1600
60°	1005
65°	724
70°	288
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 5161 cd/sqm



TEST NUMBER: P744001

CATALOG NUMBER: LD4D20D010-EU4DR2015309040-4LBSQW1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	742.4	40.5
10°-20°	731.0	39.9
20°-30°	238.8	13.0
30°-40°	81.3	4.4
40°-50°	27.3	1.5
50°-60°	8.2	0.4
60°-70°	2.7	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1712.2	93.5
0°-40°	1793.5	97.9
0°-60°	1829.1	99.8
0°-90°	1832.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1832.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	10427	
5°	9371	742
15°	2592	731
25°	475	239
35°	123	81
45°	33	27
55°	8	8
65°	3	3
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P744001

CATALOG NUMBER: LD4D20D010-EU4DR2015309040-4LBSQW1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	10427.1
0.5°	10427.1
1°	10414.1
1.5°	10388.1
2°	10340.7
2.5°	10277.6
3°	10188.4
3.5°	10064.0
4°	9879.3
4.5°	9654.6
5°	9371.4
5.5°	8999.0
6°	8617.4
6.5°	8180.1
7°	7752.1
7.5°	7250.7
8°	6803.1
8.5°	6352.8
9°	5936.8
9.5°	5555.2
10°	5199.6
12.5°	3733.5
15°	2592.4
17.5°	1693.6
20°	1067.8
22.5°	691.7
25°	475.4
27.5°	334.3
30°	240.5
32.5°	172.7
35°	122.6
37.5°	85.4
40°	61.3
42.5°	44.6
45°	33.4
47.5°	26.0
50°	17.6
52.5°	11.1
55°	8.4
57.5°	6.5
60°	4.6
62.5°	3.7
65°	2.8



TEST NUMBER: P744001

CATALOG NUMBER: LD4D20D010-EU4DR2015309040-4LBSQW1MW

CANDELA DISTRIBUTION (continued):

	0°
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





67.5°		1.9
70°		0.9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)