

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P744912

Luminaire Tested: LD4D25D010-EU4DR2015309035-4LBCSSQMB

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P744912  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-36)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D25D010-EU4DR2015309035-4LBCSSQMB  
Description: 4 INCH SQAURE SHALLOW CAST MATTE BLACK TRIM, WITH 20° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2491.3 lumens  
Efficiency: N/A  
Efficacy: 99.3 lumens/watt  
Spacing Criteria (0/90/45): 0.34 / 0.34 / 0.36  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 25.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight



TEST NUMBER: P744912  
CATALOG NUMBER: LD4D25D010-EU4DR2015309035-4LBCSSQMB

### Luminous Intensity Polar Plot





TEST NUMBER: P744912  
 CATALOG NUMBER: LD4D25D010-EU4DR2015309035-4LBCSSQMB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100															
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97	97	98	97	94															
2	111	108	105	102	109	106	104	101	103	101	99	100	99	97	98	96	95	94	94	98	96	91															
3	108	103	100	97	106	102	99	96	100	97	95	97	95	93	95	93	92	91	91	98	96	88															
4	105	99	96	93	103	98	95	92	96	93	91	95	92	90	93	91	89	88	88	93	91	85															
5	102	96	92	89	100	95	91	89	94	90	88	92	89	87	91	88	86	85	85	91	88	83															
6	99	93	89	86	98	92	88	86	91	87	85	90	87	84	88	86	84	83	83	88	86	81															
7	96	90	86	83	95	89	86	83	88	85	82	87	84	82	86	84	82	81	81	86	84	79															
8	94	87	83	81	93	87	83	80	86	83	80	85	82	80	84	82	80	79	79	84	82	77															
9	91	85	81	78	91	85	81	78	84	80	78	83	80	78	82	80	78	77	77	82	80	77															
10	89	83	79	76	88	82	79	76	82	78	76	81	78	76	81	78	76	75	75	81	78	75															

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1549274
5°	1397727
10°	784479
15°	398765
20°	168828
25°	77939
30°	41255
35°	22235
40°	11881
45°	7031
50°	4080
55°	2172
60°	1377
65°	982
70°	415
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 7031 cd/sqm



TEST NUMBER: P744912

CATALOG NUMBER: LD4D25D010-EU4DR2015309035-4LBCSSQMB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	1009.6	40.5
10°-20°	994.1	39.9
20°-30°	324.8	13.0
30°-40°	110.6	4.4
40°-50°	37.2	1.5
50°-60°	11.2	0.4
60°-70°	3.7	0.2
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2328.4	93.5
0°-40°	2439.0	97.9
0°-60°	2487.4	99.8
0°-90°	2491.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2491.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	14180	
5°	12744	###
15°	3525	994
25°	646	325
35°	167	111
45°	46	37
55°	11	11
65°	4	4
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P744912  
CATALOG NUMBER: LD4D25D010-EU4DR2015309035-4LBCSSQMB

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	14179.6
0.5°	14179.6
1°	14161.9
1.5°	14126.5
2°	14062.1
2.5°	13976.3
3°	13855.1
3.5°	13685.9
4°	13434.6
4.5°	13129.0
5°	12743.9
5.5°	12237.6
6°	11718.7
6.5°	11123.9
7°	10541.9
7.5°	9860.0
8°	9251.4
8.5°	8639.1
9°	8073.4
9.5°	7554.4
10°	7070.8
12.5°	5077.1
15°	3525.3
17.5°	2303.1
20°	1452.0
22.5°	940.7
25°	646.5
27.5°	454.6
30°	327.0
32.5°	234.9
35°	166.7
37.5°	116.2
40°	83.3
42.5°	60.6
45°	45.5
47.5°	35.4
50°	24.0
52.5°	15.2
55°	11.4
57.5°	8.8
60°	6.3
62.5°	5.1
65°	3.8



TEST NUMBER: P744912  
CATALOG NUMBER: LD4D25D010-EU4DR2015309035-4LBCSSQMB

**CANDELA DISTRIBUTION (continued):**

	0°
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





67.5°		2.5
70°		1.3

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)