

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P744781

Luminaire Tested: LD4D20D010-EU4DR7020359040-4LBSQW1MW

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P744781  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D20D010-EU4DR7020359040-4LBSQW1MW  
Description: 4 INCH SQAURE DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 70° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1661.1 lumens  
Efficiency: N/A  
Efficacy: 71.9 lumens/watt  
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 23.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight



TEST NUMBER: P744781  
CATALOG NUMBER: LD4D20D010-EU4DR7020359040-4LBSQW1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P744781

CATALOG NUMBER: LD4D20D010-EU4DR7020359040-4LBSQW1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	88	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	204055
5°	198002
10°	192481
15°	189954
20°	177374
25°	133250
30°	94206
35°	33372
40°	17543
45°	18681
50°	19344
55°	19716
60°	19842
65°	19416
70°	18337
75°	16970
80°	15038
85°	12160

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 57.5°  
 Luminance: 19847 cd/sqm



TEST NUMBER: P744781

CATALOG NUMBER: LD4D20D010-EU4DR7020359040-4LBSQW1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	170.3	10.3
10°-20°	467.1	28.1
20°-30°	514.4	31.0
30°-40°	196.6	11.8
40°-50°	92.8	5.6
50°-60°	92.3	5.6
60°-70°	73.9	4.4
70°-80°	42.4	2.6
80°-90°	11.5	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1151.7	69.3
0°-40°	1348.3	81.2
0°-60°	1533.4	92.3
0°-90°	1661.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1661.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1868	
5°	1805	170
15°	1679	467
25°	1105	514
35°	250	197
45°	121	93
55°	104	92
65°	75	74
75°	40	42
85°	10	11
90°	0	



TEST NUMBER: P744781

CATALOG NUMBER: LD4D20D010-EU4DR7020359040-4LBSQW1MW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1867.6
2.5°	1848.2
5°	1805.3
7.5°	1769.5
10°	1734.9
12.5°	1705.6
15°	1679.3
17.5°	1615.7
20°	1525.5
22.5°	1331.0
25°	1105.3
27.5°	962.2
30°	746.7
32.5°	482.3
35°	250.2
37.5°	135.2
40°	123.0
42.5°	122.2
45°	120.9
47.5°	118.3
50°	113.8
52.5°	108.8
55°	103.5
57.5°	97.6
60°	90.8
62.5°	83.1
65°	75.1
67.5°	66.2
70°	57.4
72.5°	48.5
75°	40.2
77.5°	31.6
80°	23.9
82.5°	16.8
85°	9.7
87.5°	3.8
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)