

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P744169

Luminaire Tested: LD4D20D010-EU4DR3020359050-4LBSQW1B

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P744169
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D20D010-EU4DR3020359050-4LBSQW1B
Description: 4 INCH SQAURE DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 30° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1465.9 lumens
Efficiency: N/A
Efficacy: 63.5 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.49
Luminous Opening: Rectangular (W 0.38' x L: 0.38' x H: 0')
CIE Type: Direct

Input Watts (W): 23.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P744169

CATALOG NUMBER: LD4D20D010-EU4DR3020359050-4LBSQW1B

Luminous Intensity Polar Plot





TEST NUMBER: P744169

CATALOG NUMBER: LD4D20D010-EU4DR3020359050-4LBSQW1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96																			
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92																			
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89																			
4	103	98	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85																			
5	100	94	89	86	98	93	89	86	91	88	85	90	86	84	88	86	83	82																			
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79																			
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77																			
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74																			
9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73	72																			
10	85	78	74	71	85	78	74	71	77	73	71	76	73	71	76	73	70	69																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	360810	360810	360810
5°	350448	350041	350471
10°	303544	301399	303474
15°	198045	196984	195993
20°	98480	102178	98350
25°	49610	55935	48596
30°	19860	21645	17306
35°	9213	8821	7391
40°	3977	4416	3747
45°	2804	3475	2825
50°	965	2536	1012
55°	560	1041	587
60°	383	459	383
65°	254	254	254
70°	157	112	157
75°	0	59	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°
 Vertical Angle: 45°
 Luminance: 3475 cd/sqm



TEST NUMBER: P744169

CATALOG NUMBER: LD4D20D010-EU4DR3020359050-4LBSQW1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	414.5	28.3
10°-20°	667.6	45.5
20°-30°	288.5	19.7
30°-40°	65.7	4.5
40°-50°	22.6	1.5
50°-60°	5.5	0.4
60°-70°	1.4	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1370.5	93.5
0°-40°	1436.3	98.0
0°-60°	1464.4	99.9
0°-90°	1465.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1465.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4714	4714	4714	4714	4714	
5°	4561	4557	4556	4565	4561	415
15°	2499	2469	2486	2478	2473	669
25°	587	610	662	594	575	281
35°	99	101	94	94	79	67
45°	26	32	32	32	26	18
55°	4	4	8	5	4	4
65°	1	1	1	1	1	1
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	



TEST NUMBER: P744169

CATALOG NUMBER: LD4D20D010-EU4DR3020359050-4LBSQW1B

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4713.8	4713.8	4713.8	4713.8	4713.8
2.5°	4682.6	4679.3	4681.1	4683.5	4684.4
5°	4561.0	4556.6	4555.7	4565.2	4561.3
7.5°	4315.9	4309.7	4300.2	4321.7	4341.9
10°	3905.4	3898.5	3877.8	3888.0	3904.5
12.5°	3299.3	3276.8	3276.4	3308.7	3304.4
15°	2499.2	2469.1	2485.8	2477.7	2473.3
17.5°	1680.6	1669.1	1691.3	1684.6	1655.7
20°	1209.0	1212.0	1254.4	1233.0	1207.4
22.5°	882.2	893.1	943.3	888.5	868.3
25°	587.4	609.6	662.3	594.1	575.4
27.5°	361.2	371.4	424.9	356.7	346.5
30°	224.7	219.6	244.9	210.2	195.8
32.5°	147.4	140.9	149.0	133.8	122.2
35°	98.6	100.7	94.4	93.7	79.1
37.5°	61.5	70.8	62.5	66.6	50.9
40°	39.8	51.4	44.2	48.8	37.5
42.5°	32.7	39.6	36.3	38.7	33.3
45°	25.9	32.1	32.1	32.1	26.1
47.5°	14.3	21.5	27.6	22.0	15.3
50°	8.1	10.9	21.3	11.3	8.5
52.5°	5.6	6.2	14.6	6.5	5.8
55°	4.2	4.4	7.8	4.6	4.4
57.5°	3.3	3.5	4.2	3.5	3.3
60°	2.5	2.5	3.0	2.8	2.5
62.5°	1.8	1.8	2.1	1.8	1.8
65°	1.4	1.4	1.4	1.4	1.4
67.5°	0.7	0.9	0.9	0.9	0.9
70°	0.7	0.5	0.5	0.5	0.7
72.5°	0.5	0.2	0.2	0.2	0.2
75°	0.0	0.0	0.2	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - - 90°-270°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)