

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P745380

Luminaire Tested: LD4D25D010-EU4DR5020359035-4LBCSSQMB

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P745380
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-44)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D25D010-EU4DR5020359035-4LBCSSQMB
Description: 4 INCH SQAURE SHALLOW CAST MATTE BLACK TRIM, WITH 50° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2519.6 lumens
Efficiency: N/A
Efficacy: 100.4 lumens/watt
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.73
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 25.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P745380
CATALOG NUMBER: LD4D25D010-EU4DR5020359035-4LBCSSQMB

Luminous Intensity Polar Plot





TEST NUMBER: P745380
 CATALOG NUMBER: LD4D25D010-EU4DR5020359035-4LBCSSQMB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				
1	114	112	109	107	112	110	108	106	106	104	102	102	101	99	98	97	97	95				
2	109	105	101	98	107	103	100	97	100	98	95	97	95	93	95	93	91	90				
3	105	99	95	91	103	98	94	90	95	92	89	93	90	88	91	88	86	85				
4	100	94	89	85	99	93	88	85	90	87	84	89	85	83	87	84	82	80				
5	96	89	84	80	95	88	83	79	86	82	79	85	81	78	83	80	77	76				
6	92	84	79	75	91	83	79	75	82	78	74	81	77	74	79	76	74	72				
7	88	80	75	71	87	79	74	71	78	74	71	77	73	70	76	73	70	69				
8	85	76	71	67	84	76	71	67	75	70	67	74	70	67	73	69	66	65				
9	81	73	68	64	80	72	67	64	71	67	64	71	67	64	70	66	63	62				
10	78	70	64	61	77	69	64	61	68	64	61	68	64	61	67	63	60	59				

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	443577
5°	438921
10°	431692
15°	393097
20°	327099
25°	232191
30°	122896
35°	50085
40°	18599
45°	8514
50°	3485
55°	1829
60°	896
65°	259
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 8514 cd/sqm



TEST NUMBER: P745380

CATALOG NUMBER: LD4D25D010-EU4DR5020359035-4LBCSSQMB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	378.3	15.0
10°-20°	956.0	37.9
20°-30°	858.7	34.1
30°-40°	268.9	10.7
40°-50°	47.1	1.9
50°-60°	9.4	0.4
60°-70°	1.4	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2192.9	87.0
0°-40°	2461.8	97.7
0°-60°	2518.2	99.9
0°-90°	2519.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2519.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4060	
5°	4002	378
15°	3475	956
25°	1926	859
35°	376	269
45°	55	47
55°	10	9
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P745380

CATALOG NUMBER: LD4D25D010-EU4DR5020359035-4LBCSSQMB

CANDELA DISTRIBUTION (FULL):

	0°
0°	4059.8
2.5°	4039.6
5°	4001.9
7.5°	3944.4
10°	3891.0
12.5°	3719.9
15°	3475.2
17.5°	3164.4
20°	2813.2
22.5°	2406.9
25°	1926.0
27.5°	1416.0
30°	974.1
32.5°	634.3
35°	375.5
37.5°	215.7
40°	130.4
42.5°	84.9
45°	55.1
47.5°	33.5
50°	20.5
52.5°	14.0
55°	9.6
57.5°	6.5
60°	4.1
62.5°	2.4
65°	1.0
67.5°	0.3
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)