

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P738910

Luminaire Tested: LD4D02D010-EU4DR200210IC9024-4LBSQW1B

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P738910
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-36)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D02D010-EU4DR200210IC9024-4LBSQW1B
Description: 4 INCH SQAURE DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 20° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 257.6 lumens
Efficiency: N/A
Efficacy: 50.5 lumens/watt
Spacing Criteria (0/90/45): 0.34 / 0.34 / 0.36
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 5.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P738910
CATALOG NUMBER: LD4D02D010-EU4DR200210IC9024-4LBSQW1B

Luminous Intensity Polar Plot





TEST NUMBER: P738910

CATALOG NUMBER: LD4D02D010-EU4DR200210IC9024-4LBSQW1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97	97	98	97																
2	111	108	105	102	109	106	104	101	103	101	99	100	99	97	98	96	95	94	98	96	95																
3	108	103	100	97	106	102	99	96	100	97	95	97	95	93	95	93	92	91	95	93	92																
4	105	99	96	93	103	98	95	92	96	93	91	95	92	90	93	91	89	88	93	91	89																
5	102	96	92	89	100	95	91	89	93	90	88	92	89	87	91	88	86	85	91	88	86																
6	99	93	89	86	98	92	88	86	91	87	85	90	87	84	88	86	84	83	88	86	84																
7	96	90	86	83	95	89	86	83	88	85	82	87	84	82	86	84	82	81	86	84	82																
8	94	87	83	81	93	87	83	80	86	83	80	85	82	80	84	82	80	79	84	82	80																
9	91	85	81	78	91	85	81	78	84	80	78	83	80	78	82	80	78	77	82	80	78																
10	89	83	79	76	88	82	79	76	82	78	76	81	78	76	81	78	76	75	81	78	76																

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	160154
5°	144490
10°	81091
15°	41219
20°	17453
25°	8053
30°	4264
35°	2294
40°	1227
45°	726
50°	425
55°	229
60°	153
65°	103
70°	32
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 726 cd/sqm



TEST NUMBER: P738910

CATALOG NUMBER: LD4D02D010-EU4DR200210IC9024-4LBSQW1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	104.4	40.5
10°-20°	102.8	39.9
20°-30°	33.6	13.0
30°-40°	11.4	4.4
40°-50°	3.9	1.5
50°-60°	1.2	0.5
60°-70°	0.4	0.2
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	240.7	93.5
0°-40°	252.1	97.9
0°-60°	257.1	99.8
0°-90°	257.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	257.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1466	
5°	1317	104
15°	364	103
25°	67	34
35°	17	11
45°	5	4
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P738910

CATALOG NUMBER: LD4D02D010-EU4DR200210IC9024-4LBSQW1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	1465.8
0.5°	1465.8
1°	1464.0
1.5°	1460.3
2°	1453.7
2.5°	1444.8
3°	1432.3
3.5°	1414.8
4°	1388.8
4.5°	1357.2
5°	1317.4
5.5°	1265.1
6°	1211.4
6.5°	1149.9
7°	1089.8
7.5°	1019.3
8°	956.4
8.5°	893.1
9°	834.6
9.5°	780.9
10°	730.9
12.5°	524.8
15°	364.4
17.5°	238.1
20°	150.1
22.5°	97.2
25°	66.8
27.5°	47.0
30°	33.8
32.5°	24.3
35°	17.2
37.5°	12.0
40°	8.6
42.5°	6.3
45°	4.7
47.5°	3.7
50°	2.5
52.5°	1.6
55°	1.2
57.5°	0.9
60°	0.7
62.5°	0.5
65°	0.4



TEST NUMBER: P738910
CATALOG NUMBER: LD4D02D010-EU4DR200210IC9024-4LBSQW1B

CANDELA DISTRIBUTION (continued):

	0°
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



67.5°		0.3
70°		0.1

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)