

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P745703

Luminaire Tested: LD4D25D010-EU4DR7020359035-4LBSQW1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P745703
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D25D010-EU4DR7020359035-4LBSQW1B
Description: 4 INCH SQAURE DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1568.4 lumens
Efficiency: N/A
Efficacy: 62.5 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 25.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P745703

CATALOG NUMBER: LD4D25D010-EU4DR7020359035-4LBSQW1B

Luminous Intensity Polar Plot





TEST NUMBER: P745703

CATALOG NUMBER: LD4D25D010-EU4DR7020359035-4LBSQW1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	192670
5°	186946
10°	181730
15°	179344
20°	167468
25°	125812
30°	88945
35°	31505
40°	16559
45°	17646
50°	18273
55°	18611
60°	18727
65°	18330
70°	17283
75°	16042
80°	14220
85°	11533

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 18729 cd/sqm



TEST NUMBER: P745703

CATALOG NUMBER: LD4D25D010-EU4DR7020359035-4LBSQW1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	160.8	10.3
10°-20°	441.0	28.1
20°-30°	485.7	31.0
30°-40°	185.6	11.8
40°-50°	87.6	5.6
50°-60°	87.1	5.6
60°-70°	69.7	4.4
70°-80°	40.1	2.6
80°-90°	10.9	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1087.4	69.3
0°-40°	1273.0	81.2
0°-60°	1447.7	92.3
0°-90°	1568.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1568.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1763	
5°	1704	161
15°	1586	441
25°	1044	486
35°	236	186
45°	114	88
55°	98	87
65°	71	70
75°	38	40
85°	9	11
90°	0	



TEST NUMBER: P745703

CATALOG NUMBER: LD4D25D010-EU4DR7020359035-4LBSQW1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	1763.4
2.5°	1744.9
5°	1704.5
7.5°	1670.7
10°	1638.0
12.5°	1610.4
15°	1585.5
17.5°	1525.5
20°	1440.3
22.5°	1256.7
25°	1043.6
27.5°	908.5
30°	705.0
32.5°	455.4
35°	236.2
37.5°	127.6
40°	116.1
42.5°	115.3
45°	114.2
47.5°	111.7
50°	107.5
52.5°	102.7
55°	97.7
57.5°	92.1
60°	85.7
62.5°	78.4
65°	70.9
67.5°	62.6
70°	54.1
72.5°	45.8
75°	38.0
77.5°	29.9
80°	22.6
82.5°	15.9
85°	9.2
87.5°	3.6
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)