

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P744926

Luminaire Tested: LD4D25D010-EU4DR2015309040-4LBCSSQMMS

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P744926
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-36)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D25D010-EU4DR2015309040-4LBCSSQMMS
Description: 4 INCH SQAURE SHALLOW CAST MATTE METALLIC SILVER TRIM, WITH 20° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2560.2 lumens
Efficiency: N/A
Efficacy: 102.0 lumens/watt
Spacing Criteria (0/90/45): 0.34 / 0.34 / 0.36
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 25.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P744926

CATALOG NUMBER: LD4D25D010-EU4DR2015309040-4LBCSSQMMS

Luminous Intensity Polar Plot





TEST NUMBER: P744926

CATALOG NUMBER: LD4D25D010-EU4DR2015309040-4LBCSSQMMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20								
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR																																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100									100																		
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97	98	96	95	94	93	92	91	90	89	88	87	86															
2	111	108	105	102	109	106	104	101	103	101	99	100	99	97	98	96	95	94	93	92	91	90	89	88	87	86	85	84	83	82															
3	108	103	100	97	106	102	99	96	100	97	95	97	95	93	95	93	92	91	90	89	88	87	86	85	84	83	82	81	80	79															
4	105	99	96	93	103	98	95	92	96	93	91	95	92	90	93	91	89	88	87	86	85	84	83	82	81	80	79	78	77	76															
5	102	96	92	89	100	95	91	89	94	90	88	92	89	87	91	88	86	85	84	83	82	81	80	79	78	77	76	75	74	73															
6	99	93	89	86	98	92	88	86	91	87	85	90	87	84	88	86	84	83	82	81	80	79	78	77	76	75	74	73	72	71															
7	96	90	86	83	95	89	86	83	88	85	82	87	84	82	86	84	82	81	80	79	78	77	76	75	74	73	72	71	70	69															
8	94	87	83	81	93	87	83	80	86	83	80	85	82	80	84	82	80	79	78	77	76	75	74	73	72	71	70	69	68	67															
9	91	85	81	78	91	85	81	78	84	80	78	83	80	78	82	80	78	77	76	75	74	73	72	71	70	69	68	67	66	65															
10	89	83	79	76	88	82	79	76	82	78	76	81	78	76	81	78	76	75	74	73	72	71	70	69	68	67	66	65	64	63															

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1592104
5°	1436377
10°	806169
15°	409793
20°	173502
25°	80097
30°	42404
35°	22848
40°	12209
45°	7216
50°	4198
55°	2229
60°	1420
65°	1008
70°	415
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 7216 cd/sqm



TEST NUMBER: P744926

CATALOG NUMBER: LD4D25D010-EU4DR2015309040-4LBCSSQMMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1037.5	40.5
10°-20°	1021.6	39.9
20°-30°	333.7	13.0
30°-40°	113.6	4.4
40°-50°	38.2	1.5
50°-60°	11.5	0.5
60°-70°	3.8	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2392.8	93.5
0°-40°	2506.4	97.9
0°-60°	2556.2	99.8
0°-90°	2560.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2560.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	14572	
5°	13096	###
15°	3623	1022
25°	664	334
35°	171	114
45°	47	38
55°	12	12
65°	4	4
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P744926

CATALOG NUMBER: LD4D25D010-EU4DR2015309040-4LBCSSQMMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	14571.6
0.5°	14571.6
1°	14553.5
1.5°	14517.1
2°	14450.9
2.5°	14362.7
3°	14238.1
3.5°	14064.3
4°	13806.1
4.5°	13492.0
5°	13096.3
5.5°	12576.0
6°	12042.7
6.5°	11431.5
7°	10833.3
7.5°	10132.7
8°	9507.2
8.5°	8877.9
9°	8296.6
9.5°	7763.3
10°	7266.3
12.5°	5217.5
15°	3622.8
17.5°	2366.8
20°	1492.2
22.5°	966.7
25°	664.4
27.5°	467.1
30°	336.1
32.5°	241.3
35°	171.3
37.5°	119.4
40°	85.6
42.5°	62.3
45°	46.7
47.5°	36.3
50°	24.7
52.5°	15.6
55°	11.7
57.5°	9.1
60°	6.5
62.5°	5.2
65°	3.9



TEST NUMBER: P744926

CATALOG NUMBER: LD4D25D010-EU4DR2015309040-4LBCSSQMMS

CANDELA DISTRIBUTION (continued):

	0°
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





67.5°		2.6
70°		1.3

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)