

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P745561

Luminaire Tested: LD4D25D010-EU4DR6020359040-4LBSQW1MW

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P745561
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D25D010-EU4DR6020359040-4LBSQW1MW
Description: 4 INCH SQAURE DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2330.2 lumens
Efficiency: N/A
Efficacy: 92.8 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 25.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P745561
CATALOG NUMBER: LD4D25D010-EU4DR6020359040-4LBSQW1MW

Luminous Intensity Polar Plot





TEST NUMBER: P745561

CATALOG NUMBER: LD4D25D010-EU4DR6020359040-4LBSQW1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93			93																
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86			86																
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80			80																
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75			75																
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70			70																
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66			66																
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62			62																
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59			59																
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55			55																
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53			53																

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	302379
5°	309808
10°	313545
15°	298703
20°	263358
25°	213010
30°	144091
35°	72200
40°	11710
45°	11465
50°	11695
55°	11868
60°	12194
65°	12461
70°	12778
75°	12918
80°	12458
85°	10405

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 75°
 Luminance: 12918 cd/sqm



TEST NUMBER: P745561

CATALOG NUMBER: LD4D25D010-EU4DR6020359040-4LBSQW1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	270.0	11.6
10°-20°	730.4	31.3
20°-30°	785.9	33.7
30°-40°	341.6	14.7
40°-50°	57.4	2.5
50°-60°	55.8	2.4
60°-70°	47.7	2.0
70°-80°	31.9	1.4
80°-90°	9.5	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1786.3	76.7
0°-40°	2127.9	91.3
0°-60°	2241.0	96.2
0°-90°	2330.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2330.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2768	
5°	2825	270
15°	2641	730
25°	1767	786
35°	541	342
45°	74	57
55°	62	56
65°	48	48
75°	31	32
85°	8	10
90°	0	



TEST NUMBER: P745561

CATALOG NUMBER: LD4D25D010-EU4DR6020359040-4LBSQW1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	2767.5
2.5°	2845.3
5°	2824.7
7.5°	2831.2
10°	2826.1
12.5°	2767.8
15°	2640.7
17.5°	2470.0
20°	2265.0
22.5°	2045.7
25°	1766.9
27.5°	1413.2
30°	1142.1
32.5°	880.2
35°	541.3
37.5°	231.6
40°	82.1
42.5°	75.6
45°	74.2
47.5°	71.7
50°	68.8
52.5°	65.5
55°	62.3
57.5°	59.1
60°	55.8
62.5°	52.2
65°	48.2
67.5°	44.3
70°	40.0
72.5°	35.3
75°	30.6
77.5°	25.2
80°	19.8
82.5°	14.0
85°	8.3
87.5°	2.9
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)