

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P738859

Luminaire Tested: LD4D02D010-EU4DR150210IC9030-4LBSQW1MW

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P738859  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-21)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D02D010-EU4DR150210IC9030-4LBSQW1MW  
Description: 4 INCH SQAURE DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 15° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 319.7 lumens  
Efficiency: N/A  
Efficacy: 62.7 lumens/watt  
Spacing Criteria (0/90/45): 0.22 / 0.22 / 0.23  
Luminous Opening: Vertical Cylinder (Dia: 0.35' x H: 0.35')  
CIE Type: Direct

Input Watts (W): 5.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight



TEST NUMBER: P738859  
CATALOG NUMBER: LD4D02D010-EU4DR150210IC9030-4LBSQW1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P738859

CATALOG NUMBER: LD4D02D010-EU4DR150210IC9030-4LBSQW1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100															
1	116	114	112	111	113	112	110	109	108	107	106	104	103	103	101	100	100	98				98															
2	113	110	107	105	111	108	106	104	105	103	102	102	101	100	100	98	98	96				96															
3	110	106	103	101	108	105	102	100	103	100	99	100	99	97	98	97	96	94				94															
4	108	103	100	98	106	102	99	97	100	98	96	99	97	95	97	95	94	93				93															
5	106	101	98	95	104	100	97	95	98	96	94	97	95	93	96	94	92	92				92															
6	104	99	95	93	102	98	95	93	97	94	92	96	93	92	95	93	91	90				90															
7	102	97	93	91	101	96	93	91	95	93	91	94	92	90	93	91	90	89				89															
8	100	95	92	90	99	95	92	90	94	91	89	93	91	89	92	90	89	88				88															
9	99	93	90	88	98	93	90	88	92	90	88	92	89	88	91	89	87	87				87															
10	97	92	89	87	96	92	89	87	91	89	87	91	88	87	90	88	86	86				86															

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	490137	490137	490137
5°	288026	284297	286543
10°	85964	86561	87886
15°	21384	21801	21124
20°	6399	7405	6529
25°	2259	2875	2282
30°	831	1093	839
35°	414	472	399
40°	263	291	263
45°	196	210	196
50°	153	153	153
55°	125	125	125
60°	105	105	105
65°	79	79	79
70°	66	66	66
75°	45	45	53
80°	32	32	32
85°	17	17	17

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 45°

Vertical Angle: 45°

Luminance: 210 cd/sqm



TEST NUMBER: P738859

CATALOG NUMBER: LD4D02D010-EU4DR150210IC9030-4LBSQW1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	207.4	64.9
10°-20°	85.3	26.7
20°-30°	16.9	5.3
30°-40°	4.2	1.3
40°-50°	2.2	0.7
50°-60°	1.6	0.5
60°-70°	1.2	0.4
70°-80°	0.7	0.2
80°-90°	0.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	309.6	96.8
0°-40°	313.8	98.1
0°-60°	317.7	99.4
0°-90°	319.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	319.7	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	4356	4356	4356	4356	4356	
5°	2834	2805	2797	2817	2820	207
15°	246	251	251	246	243	84
25°	29	33	37	33	29	15
35°	6	6	6	6	6	4
45°	3	3	3	3	3	2
55°	2	2	2	2	2	2
65°	1	1	1	1	1	1
75°	1	1	1	1	1	1
85°	0	0	0	0	0	0
90°	0	0	0	0	0	



TEST NUMBER: P738859

CATALOG NUMBER: LD4D02D010-EU4DR150210IC9030-4LBSQW1MW

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	4356.0	4356.0	4356.0	4356.0	4356.0
2.5°	3929.3	3932.6	3933.9	3937.8	3952.2
5°	2834.1	2805.0	2797.4	2816.8	2819.5
7.5°	1678.8	1684.7	1706.3	1711.1	1693.8
10°	921.3	928.8	927.7	934.4	941.9
12.5°	471.2	465.3	463.4	471.0	460.5
15°	246.2	250.8	251.0	246.5	243.2
17.5°	132.4	137.8	146.6	139.4	128.3
20°	78.2	83.0	90.5	84.6	79.8
22.5°	48.3	52.2	57.5	52.9	49.1
25°	29.0	32.8	36.9	32.6	29.3
27.5°	17.1	20.5	23.1	20.3	17.0
30°	11.1	12.9	14.6	12.7	11.2
32.5°	7.7	8.5	9.2	8.5	7.7
35°	5.7	6.1	6.5	6.1	5.5
37.5°	4.4	4.8	5.0	4.6	4.2
40°	3.7	3.9	4.1	3.9	3.7
42.5°	3.1	3.3	3.3	3.3	3.1
45°	2.8	2.8	3.0	2.8	2.8
47.5°	2.4	2.4	2.6	2.4	2.4
50°	2.2	2.2	2.2	2.2	2.2
52.5°	2.0	2.0	2.0	2.0	2.0
55°	1.8	1.8	1.8	1.8	1.8
57.5°	1.7	1.7	1.7	1.7	1.7
60°	1.5	1.5	1.5	1.5	1.5
62.5°	1.3	1.3	1.3	1.3	1.3
65°	1.1	1.1	1.1	1.1	1.1
67.5°	1.1	1.1	1.1	1.1	1.1
70°	0.9	0.9	0.9	0.9	0.9
72.5°	0.7	0.7	0.7	0.7	0.7
75°	0.6	0.6	0.6	0.6	0.7
77.5°	0.6	0.6	0.6	0.6	0.6
80°	0.4	0.4	0.4	0.4	0.4
82.5°	0.4	0.4	0.4	0.4	0.4
85°	0.2	0.2	0.2	0.2	0.2
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report







— 0°-180°    - - 45°-225°    - - - - 90°-270°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)