

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P745810

Luminaire Tested: LD4D30D010-EU4DR2015309024-4LBCSSQMMS

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P745810  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-36)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D30D010-EU4DR2015309024-4LBCSSQMMS  
Description: 4 INCH SQAURE SHALLOW CAST MATTE METALLIC SILVER TRIM, WITH 20° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2314.0 lumens  
Efficiency: N/A  
Efficacy: 79.8 lumens/watt  
Spacing Criteria (0/90/45): 0.34 / 0.34 / 0.36  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 29  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight



TEST NUMBER: P745810  
CATALOG NUMBER: LD4D30D010-EU4DR2015309024-4LBCSSQMMS

### Luminous Intensity Polar Plot





TEST NUMBER: P745810

CATALOG NUMBER: LD4D30D010-EU4DR2015309024-4LBCSSQMMS

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |     | 30  |     |     |     | 10  | 0   |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 0   |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |
| 1   | 115 | 113 | 111 | 109 | 113 | 111 | 109 | 108 | 107 | 106 | 104 | 103 | 102 | 101 | 100 | 99  | 98  | 97  |
| 2   | 111 | 108 | 105 | 102 | 109 | 106 | 104 | 101 | 103 | 101 | 99  | 100 | 99  | 97  | 98  | 96  | 95  | 94  |
| 3   | 108 | 103 | 100 | 97  | 106 | 102 | 99  | 96  | 100 | 97  | 95  | 97  | 95  | 93  | 95  | 93  | 92  | 91  |
| 4   | 105 | 99  | 96  | 93  | 103 | 98  | 95  | 92  | 96  | 93  | 91  | 95  | 92  | 90  | 93  | 91  | 89  | 88  |
| 5   | 102 | 96  | 92  | 89  | 100 | 95  | 91  | 89  | 94  | 90  | 88  | 92  | 89  | 87  | 91  | 88  | 86  | 85  |
| 6   | 99  | 93  | 89  | 86  | 98  | 92  | 88  | 86  | 91  | 87  | 85  | 90  | 87  | 84  | 88  | 86  | 84  | 83  |
| 7   | 96  | 90  | 86  | 83  | 95  | 89  | 86  | 83  | 88  | 85  | 82  | 87  | 84  | 82  | 86  | 84  | 82  | 81  |
| 8   | 94  | 87  | 83  | 81  | 93  | 87  | 83  | 80  | 86  | 83  | 80  | 85  | 82  | 80  | 84  | 82  | 80  | 79  |
| 9   | 91  | 85  | 81  | 78  | 91  | 85  | 81  | 78  | 84  | 80  | 78  | 83  | 80  | 78  | 82  | 80  | 78  | 77  |
| 10  | 89  | 83  | 79  | 76  | 88  | 82  | 79  | 76  | 82  | 78  | 76  | 81  | 78  | 76  | 81  | 78  | 76  | 75  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |         |
|-----|---------|
|     | 0°      |
| 0°  | 1439062 |
| 5°  | 1298304 |
| 10° | 728684  |
| 15° | 370395  |
| 20° | 156829  |
| 25° | 72394   |
| 30° | 38328   |
| 35° | 20648   |
| 40° | 11040   |
| 45° | 6521    |
| 50° | 3791    |
| 55° | 2019    |
| 60° | 1289    |
| 65° | 905     |
| 70° | 383     |
| 75° | 0       |
| 80° | 0       |
| 85° | 0       |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 6521 cd/sqm



TEST NUMBER: P745810

CATALOG NUMBER: LD4D30D010-EU4DR2015309024-4LBCSSQMMS

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 937.7  | 40.5      |
| 10°-20°   | 923.4  | 39.9      |
| 20°-30°   | 301.7  | 13.0      |
| 30°-40°   | 102.7  | 4.4       |
| 40°-50°   | 34.5   | 1.5       |
| 50°-60°   | 10.4   | 0.5       |
| 60°-70°   | 3.5    | 0.1       |
| 70°-80°   | 0.2    | 0.0       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 2162.8 | 93.5      |
| 0°-40°    | 2265.5 | 97.9      |
| 0°-60°    | 2310.4 | 99.8      |
| 0°-90°    | 2314.0 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 2314.0 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°    | Flux |
|-----|-------|------|
| 0°  | 13171 |      |
| 5°  | 11837 | 938  |
| 15° | 3274  | 923  |
| 25° | 600   | 302  |
| 35° | 155   | 103  |
| 45° | 42    | 35   |
| 55° | 11    | 10   |
| 65° | 4     | 3    |
| 75° | 0     | 0    |
| 85° | 0     | 0    |
| 90° | 0     |      |



TEST NUMBER: P745810

CATALOG NUMBER: LD4D30D010-EU4DR2015309024-4LBCSSQMMS

**CANDELA DISTRIBUTION (FULL):**

|       | 0°      |
|-------|---------|
| 0°    | 13170.9 |
| 0.5°  | 13170.9 |
| 1°    | 13154.5 |
| 1.5°  | 13121.6 |
| 2°    | 13061.8 |
| 2.5°  | 12982.1 |
| 3°    | 12869.5 |
| 3.5°  | 12712.3 |
| 4°    | 12478.9 |
| 4.5°  | 12195.1 |
| 5°    | 11837.4 |
| 5.5°  | 11367.1 |
| 6°    | 10885.0 |
| 6.5°  | 10332.6 |
| 7°    | 9792.0  |
| 7.5°  | 9158.6  |
| 8°    | 8593.3  |
| 8.5°  | 8024.5  |
| 9°    | 7499.1  |
| 9.5°  | 7017.0  |
| 10°   | 6567.9  |
| 12.5° | 4716.0  |
| 15°   | 3274.5  |
| 17.5° | 2139.2  |
| 20°   | 1348.8  |
| 22.5° | 873.8   |
| 25°   | 600.5   |
| 27.5° | 422.2   |
| 30°   | 303.8   |
| 32.5° | 218.1   |
| 35°   | 154.8   |
| 37.5° | 107.9   |
| 40°   | 77.4    |
| 42.5° | 56.3    |
| 45°   | 42.2    |
| 47.5° | 32.8    |
| 50°   | 22.3    |
| 52.5° | 14.1    |
| 55°   | 10.6    |
| 57.5° | 8.2     |
| 60°   | 5.9     |
| 62.5° | 4.7     |
| 65°   | 3.5     |



TEST NUMBER: P745810  
CATALOG NUMBER: LD4D30D010-EU4DR2015309024-4LBCSSQMMS

**CANDELA DISTRIBUTION (continued):**

|       | 0°  |
|-------|-----|
| 72.5° | 0.0 |
| 75°   | 0.0 |
| 77.5° | 0.0 |
| 80°   | 0.0 |
| 82.5° | 0.0 |
| 85°   | 0.0 |
| 87.5° | 0.0 |
| 90°   | 0.0 |

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





|       |  |     |
|-------|--|-----|
| 67.5° |  | 2.3 |
| 70°   |  | 1.2 |

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)